



Part Number : [2044734212](#)

Product Description : DDR5 RDIMM Socket, Vertical Surface Mount, 0.76µm Gold Plating, 288 Circuits, PCB Thickness 1.57mm to 3.18mm, Yellow Housing, Off-White Latch

Series Number : 204473

Status : Active

Product Category : Memory Module Connectors



Documents and Resources

Drawings

[2044734212 sd.pdf](#)


Specifications

[2044730000-AS-000.pdf](#)

[2044730002-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Memory Module Connectors
Series	204473
Description	DDR5 RDIMM Socket, Vertical Surface Mount, 0.76µm Gold Plating, 288 Circuits, PCB Thickness 1.57mm to 3.18mm, Yellow Housing, Off-White Latch
Component Type	Socket
JEDEC Outline	MO-329
Product Name	DDR5 DIMM
UPC	195842754942

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	29V AC (RMS)/DC

Physical

Circuits (Loaded)	288
Circuits (maximum)	288
Durability (mating cycles max)	25
Entry Angle	Vertical (Top Entry)

Flammability	94V-0
Housing Color	Yellow
Keying to Mating Part	Yes
Latch Color	Natural (Off-White)
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Polyamide
Net Weight	6.289/g
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm, 3.18mm
Pitch - Mating Interface	0.85mm
Pitch - Termination Interface	0.85mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Memory Module Cards of 1.27mm Thickness

This document was generated on Apr 11, 2026