
Part Number : 1200310004
Product Description : Nano-Change (M8) Receptacle, 3 Poles, A-Coded, M8 x 0.5 Mounting Threads, Male (Straight) to 22 AWG Leads, 0.30m (11.81") Length
Series Number : 120031
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 4R3F06E02C3003



Documents and Resources

Drawings

1200310004_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate; Lead monoxide per D(2024)7663-DC (21 Jan 2025) SCIP:4c156919-516b-4896-8199-28750b7dd2f5
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Connectors
Series	120031
Description	Nano-Change (M8) Receptacle, 3 Poles, A-Coded, M8 x 0.5 Mounting Threads, Male (Straight) to 22 AWG Leads, 0.30m (11.81") Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Nano-Change (M8)
Type	Single Ended (pigtail)
UPC	883906177775

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Coupling Type	External Thread
Gender	Male
Keyway	A-Coded
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M8 x 0.5

Downloaded from Arrow.com.

Net Weight	84.790/g
Orientation	Straight
Panel Mount	Front
Poles	3
Temperature Range - Operating	-25° to +90°C
Wire/Cable Type	UL 1569
Wire Size (AWG)	24

Downloaded from Arrow.com.