




Multilayer Ceramic Chip Capacitor

Part Number: 111122K00330GQTA9LM

Description: 1111 2000Vdc 33pF ±2% C0G - Hi Q/Low ESR Non-Mag (PME)

Ultra stable HighQ Low ESR multi-layer ceramic capacitors offering very stable $0\pm30\text{ppm}/^\circ\text{C}$, $0\pm15\text{ppm}/^\circ\text{C}$ or $+90\pm20\text{ppm}/^\circ\text{C}$ High Q material systems that provide excellent low loss performance and guaranteed non-magnetic / relative permeability of 1.000 for critical applications such as NMR / MRI. Optimised for the lowest possible ESR and with maximised voltage ratings, this range provides the best possible conduction of high power RF signals.



Mechanical Specification

Size Code	1111
Length (L1) in mm (")	$2.79 +0.51/-0.25$ (0.11 +0.02/-0.01)
Width (W) in mm (")	2.79 ± 0.38 (0.113 ± 0.015)
Thickness (T) in mm (")	2.0 ± 0.2 (0.08 ± 0.008)
Minimum Termination Band (L2,L3) in mm (")	0.13 (0.005)
Maximum Termination Band (L2,L3) in mm (")	0.63 (0.025)
Termination Material	Copper Barrier, Sn Plated Solder (Non-Mag., RoHS compliant)
Solderability	IEC-60068-2-58
Packaging	7" Reel Horizontal Orientation, 1000 per reel

General Electrical Specification

Rated Voltage	2000Vdc
Nominal Capacitance Value	33pF
Capacitance Tolerance	±2%
Tangent of Loss Angle (Tan δ)	≤ 0.00067
Capacitance and Tan δ Test Conditions	1.0Vrms @ 1MHz
Voltage Proof	2400Vdc
(Voltage applied for 5 secs max. @ 50mA max. charge current)	100.00GOhm @ 100Vdc
Min Insulation Resistance (IR)	C0G - Hi Q/Low ESR Non-Mag (PME)
Dielectric Classification	-55°C / +125°C
Rated Temperature Range	No DC Voltage $0\pm30\text{ppm}/^\circ\text{C}$
Maximum Capacitance Change over Temperature Range	Rated DC Voltage -
Climatic Category (IEC)	55/125/56
Ageing Characteristic	Zero

Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

www.knowlescapacitors.com

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at <http://www.knowlescapacitors.com> or by contacting us.

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and omissions excepted.

Date: Sunday, February 06, 2022

20220206 211425095UTC



Multilayer Ceramic Chip Capacitor

Part Number: 111122K00330GQTAF9LM

Description: 1111 2000Vdc 33pF ±2% C0G - Hi Q/Low ESR Non-Mag (PME)

Environmental

RoHS Compliant to 2011/65/EC as amended by 2015/863/EU

Compliant

REACH Compliant

219 compliant

California Proposition 65

No exposure risk


Board Layout

Knowles' conventional 2-terminal chip capacitors can generally be mounted using pad designs in accordance with international specification IPC-7351, Generic Requirements for Surface Mount Design and Land Pattern Standards, but there are some other factors that have been shown to reduce mechanical stress, such as reducing the pad width to less than the chip width. In addition, the position of the chip on the board should be considered.

Some high voltage parts may require modifications to the board layout and/or the addition of a conformal coating to prevent flashover. Refer to application note AN0043 for further information.

IPC-7351 pad design


1111		
C	2.80mm	0.110"
Y	1.20mm	0.047"
X	3.20mm	0.126"



Packaging

Tape packaging information for tape-and-reel parts:

Tape and reel packing of surface mounting chip capacitors for automatic placement are in accordance with IEC60286-3.



Soldering


Reflow solder in accordance with IPC-A-610. Recommended reflow profile as laid down in IPC/JEDEC J-STD-020.

Wave soldering is also possible, but care must be taken for case sizes 1210 and larger and component thickness >1.0mm. Trials are encouraged.

Hand soldering is not recommended and can lead to component damage through thermal shock.

PdAg terminations are primarily intended for conductive epoxy attachment - they may be suitable for soldering but trials are recommended.

Application notes with mounting and handling guidance are available on request.



Compex

DLI

Johanson MFG

Novacap

Syfer

Voltronics

Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at <http://www.knowlescapacitors.com> or by contacting us.

Asia: KPD-Asia-sales@knowles.com

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and omissions excepted.

USA: KPD-NA-sales@knowles.com

www.knowlescapacitors.com

Date: Sunday, February 06, 2022

20220206 211425095UTC