

**Part Number :** [1200870083](#)

**Product Description :** Nano-Change (M8) Double-Ended Cordset, 3 Poles, A-Coded, Male (Straight) to Female (Straight), 24 AWG, PVC Cable, 10.0m (32.81') Length

**Series Number :** 120087

**Status :** Obsolete

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 443030A10M100



---

## Documents and Resources

### Drawings

[1200870083\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Obsolete
Category	Circular Industrial Cordsets
Series	120087
Description	Nano-Change (M8) Double-Ended Cordset, 3 Poles, A-Coded, Male (Straight) to Female (Straight), 24 AWG, PVC Cable, 10.0m (32.81') Length
IP Rating	N/A
Product Name	Nano-Change (M8)
Protocol	N/A
Type	Double Ended
UPC	78678851055

### Agency

CSA	LR6837
UL	E152210

### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

### Physical

Cable Diameter	4.32mm (.170")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Yellow
Connector End A	Nano-Change (M8)
Connector End B	Nano-Change (M8)
Coupling Style	Threaded
Gender	Female-Male
Keyway	A-Coded

LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	32.486/g
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	24

---

This document was generated on May 16, 2026

Obsoleted