




Home> Products > MICRO SWITCH™ Toggle Switches> TL > Product Page

2TL1-56M



Actual product appearance may vary.

TL Series Toggle Switch, 2 pole, 3 position, Screw terminal, Locking Lever, Military Part Number MS27408 - 2M

Features

- Qualified to MILS-3950
- Environmentproof sealing
- 1,2, and 4 pole circuitry
- Standard and pull-to-unlock levers
- 2 and 3 position, maintained and momentary toggle action
- Temperature range:-85° F to +160° F
- Completely sealed switching chamber
- Step-design case provides added space between terminals to help prevent shorting
- UL recognized, CSA certified
- CE approved

Potential Applications


- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

Description

MICRO SWITCH™TL Series toggle switches have high strength, temperature resistant, non-tracking case material and silver cadmium oxide contacts. Pulto-Unlock toggle levers prevent accidental operation; the lever must be pulled approx. 2,3 mm (0.09 inches) to change positions.

Supporting Documentation

-  [Accessory: Seals](#)
-  [Accessory: Nuts](#)
-  [Engineering Drawing](#)

Product Specifications			
Circuitry/Operating action	<div><div>Keyway Momentary Position</div><div>Center Maintained Position</div><div>Opposite Keyway Maintained Position</div></div> <div><div><div><div><div></div><div></div></div><div>3</div><div>2</div><div>1</div></div><div><div><div><div></div><div></div></div><div>6</div><div>5</div><div>4</div></div><div>ON</div></div><div><div><div><div></div><div></div></div><div>3</div><div>2</div><div>1</div></div><div><div><div><div></div><div></div></div><div>6</div><div>5</div><div>4</div></div><div>ON</div></div><div><div><div><div></div><div></div></div><div>3</div><div>2</div><div>1</div></div><div><div><div><div></div><div></div></div><div>6</div><div>5</div><div>4</div></div><div>ON</div></div></div></div></div></div>		
Product Type	MICRO SWITCH™ Toggle Switch		
Lever Lock	<div><div>Locked out of and into extreme position (Opposite keyway)</div></div>		
Ampere/Voltage Range (Resistive Load)	0.75 A at 115 Vdc,0.5 A at 250 Vdc,0.5 A to 10 A at 0.5 Vac to 277 Vac,0.5 A to 18 A at 0.5 Vdc to 28 Vdc		
Circuitry	DPDT		
Action	3 position		
Mounting	Bushing 15/32 in		
Termination	Screw		
Military Part Number	MS27408 -2M		
Lever Type	Locking		
UL/CSA Rating Code	L192: 10 A - 125, 250, 277 Vac; 1/4 Hp - 125 Vac; 1/2 Hp - 250, 277 Vac; 3 A - 125 Vac "L"		
Comment	Silver cadmium oxide contacts		
Availability	Global		
UNSPSC Code	30211908		
UNSPSC Commodity	30211908 Toggle switches		
Series Name	TL		

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Contr

Product Search

Part number search:

Use (*) to expand search

Specification Search