




eMMC

KLM4G1FETE-B041



OVERVIEW

SPECIFICATIONS

RELATED RESOURCES

RELATED INSIGHTS

Definitive performance for mobile storage

With superior power efficiency and noticeably fast speed, Samsung's eMMC is the definitive choice for flash storage to develop slim mobile design.

Specifications

Version	eMMC 5.1	Density	4 GB
Voltage	1.8, 3.3 V / 3.3 V	Interface	HS400
Package Size	11 x 10 x 0.8 mm	Temp.	-25 ~ 85 °C
Product Status	Mass Production		

[SEE ALL](#)

Related resources



Samsung Memory



Samsung eMMC


Related insights



Samsung Enhances Functional Safety to its Automotive

The certification assures safety and reliability in Samsung's new functional safety management system across its product development process for automotive solutions.

[LEARN MORE >](#)



Samsung Electronics Doubling Current Smartphone Storage

Based on the company's fifth-generation V-NAND, the new memory meets the newest Universal Flash Storage industry specifications at a speed 20x faster than a typical microSD card.

[LEARN MORE >](#)



All product specifications reflect internal test results and are subject to variations by user's system configuration. All product images shown are for illustration purposes only and may not be an exact representation of the product. Samsung reserves the right to change product images and specifications at any time without notice.

Insights

[Product Finder](#)

[Technical Resources](#)

[TCO Calculator](#)

[About Us](#)

PRODUCTS

[DRAM](#)

[SSD](#)

[eSTORAGE](#)

[MCP](#)

[PROCESSOR](#)

[IMAGE SENSOR](#)

[SECURITY SOLUTIONS](#)

SOLUTIONS

[APPLICATIONS](#)

Other Sites

[中文\(简体\)](#)

[Samsung Business](#)

[Exynos](#)

[LED](#)

[Display](#)

[Worker Safety](#)

Follow us



DISPLAY IC

POWER IC

Copyright © 1995-2019 SAMSUNG All Rights Reserved.

PRIVACY **LEGAL** **SITEMAP**

This website is best viewed using Microsoft Internet Explorer 9 or higher, and/or latest version of Google Chrome and Mozilla Firefox browsers.