

TERMINAL BLOCKS MILITARY CLASS

38TB XX F

Replace "XX" with 02 through 23 for number of poles



Wire Range

- Recommended Maximum size wire: #14 AWG Copper Wire
- Recommended Torque: 9 in. lbs.

Electrical Ratings

- 20 AMps
- Rated Voltage (maximum): 600 Volts
- D.W.V: 3400 Volts RMS

Agency Compliance

- A-A-59125 / 2, (supercedes MIL - T-55164 / 2)
- MAI-60 in accordance with MIL - M - 14, ASTM 5948-96
- RoHS Compliant
- DFARS Compliant

Material Information


- Insulator base:
 - MAI - 60
 - Grade F temperature rating
 - Grey Color
- Terminal Plates: Brass per QQ-B-613, Nickel plated per QQ-N-290
- Screws: Brass per QQ-W-321, Nickel plated per QQ-N-290

Accessories

- Marking strips - MSA, MSB, or MSC

Product Data Sheet

Drawing



Dimensions			
Catalog No	# of Poles	A	B
38TB02F	2	1.719 - 1.610	1.341 - 1.283
38TB03F	3	2.156 - 2.047	1.778 - 1.720
38TB04F	4	2.594 - 2.485	2.216 - 2.158
38TB05F	5	3.031 - 2.922	2.653 - 2.595
38TB06F	6	3.469 - 3.360	3.091 - 3.033
38TB07F	7	3.906 - 3.797	3.528 - 3.470
38TB08F	8	4.344 - 4.235	3.966 - 3.908
38TB09F	9	4.781 - 4.672	4.403 - 4.345
38TB10F	10	5.219 - 5.100	4.841 - 4.783
38TB11F	11	5.656 - 5.537	5.298 - 5.200
38TB12F	12	6.094 - 5.975	5.736 - 5.638

Dimensions			
Catalog No	# of Poles	A	B
38TB13F	13	6.531 - 6.412	6.173 - 6.075
38TB14F	14	6.969 - 6.850	6.611 - 6.513
38TB15F	15	7.406 - 7.287	7.048 - 6.950
38TB16F	16	7.844 - 7.725	7.486 - 7.388
38TB17F	17	8.281 - 8.162	7.923 - 7.825
38TB18F	18	8.719 - 8.600	8.361 - 8.263
38TB19F	19	9.156 - 9.037	8.798 - 8.700
38TB20F	20	9.594 - 9.475	9.236 - 9.138
38TB21F	21	10.031 - 9.912	9.673 - 9.575
38TB22F	22	10.469 - 10.350	10.111 - 10.013
38TB23F	23	10.906 - 10.787	10.548 - 10.450