




Similar to illustration



Dimensions in mm

- Included:
- Powder-coated, sheet steel enclosure
 - Box with narrow beveled edge, sturdy gutter profile
 - With hinged cover 180° (PA), with foam PU seal, 2 to 3 quick disconnects
 - Quick-release fasteners in plastic bushes
 - Mounting holes (incl. sealing plugs)
 - Large Macrolon inspection glass
 - Removable, yellow-chromized interior profiles
 - Galvanized DIN-35/7.5 rail (contact with enclosure), adjustable in 12.5 mm spacing
 - Grounding lug for cover and flanges with quick-release ribbon cable connectors
 - Light gray (RAL 7035)

Accessories:
Fitted and unfitted flange plates, wall mounting

The "number of I/O modules" also takes fieldbus couplers and bus end modules into account.
This applies to 12 mm wide I/O modules. I/O modules with a width of 24 mm count as two I/O modules.

Technical data	
Number of I/O modules	16
Number of flange plates that can be fitted	1 x Size 295 x 95 mm: F300; F300-1; F300-2; F304

Physical data	
Width	300 mm / 11.811 inches
Height	120 mm / 4.724 inches
Depth	200 mm / 7.874 inches
Panel cutout (W x H)	(260 x 160) mm

Protection type	IP65
-----------------	------

Commercial data	
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143243094
Customs tariff number	8538100000

UNSPSC	39121324
eCl@ss 10.0	27-14-24-18
eCl@ss 9.0	27-14-24-18
ETIM 9.0	EC000261
ETIM 10.0	EC000261
ECCN	NO US CLASSIFICATION

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Environmental Product Compliance

Environmental Product
Compliance
850-815/002-000

System Description	
IP65 System Housing	pdf 163.66 KB ↓

Bid Text			
850-815/002-000	19.02.2019	xml 4.33 KB ↓	
850-815/002-000	09.10.2017	doc 31.50 KB ↓	



1 Compatible Products
1.1 Optional Accessories
1.1.1 Installation
1.1.1.1 Mounting accessories



Item No.: 850-904
Wall Mounting; Set with 4 brackets

1.1.1.2 System enclosure



Item No.: 850-820/000-001
Cable entry plate; Cable entry plate 22; for flange plate F204 + F304; 16 x Ø 3.0 ... 6.5 mm, 4 x Ø 5.0 ... 9.2 mm, 2 x Ø 8.0 ... 12.5 mm



Item No.: 850-820/000-002
Cable entry plate; Cable entry plate 29; for flange plate F204 + F304; 29 x Ø 3.0 ... 6.5 mm



Item No.: 850-819/002-005
Flange plate



Item No.: 850-819/002-000
Flange plate; F300 flange plate; WxH (295x95 mm); blind



Item No.: 850-819/002-002
Flange plate; F300-1 flange plate; WxH (295x95 mm); 4 x M20, 6 x M16, 22 x M12 cable grip



Item No.: 850-819/002-001
Flange plate; F300-1 flange plate; WxH (295x95 mm); 4 x M20, 6 x M16, 22 x M12 drilled holes



Item No.: 850-819/002-004
Flange plate; F300-2 flange plate; WxH (295x95 mm); 50 x M12 cable grip



Item No.: 850-819/002-003
Flange plate; F300-2 flange plate; WxH (295x95 mm); 50 x M12 drilled holes