

Part Number : 1000570183

Series Number : 100057

Product Category : Specialty Wire and Cable

Product Description : Temp-Flex High-Performance Flat-Ribbon Cable, 3 Circuits, 1.27mm Pitch, 28 AWG, Silver Plated Copper, UL 20424, 7/36 Stranded Extruded FEP, Blue with Blue Polarity Stripe

Status : Active

Engineering Number : F2807S-3-050-55

Documents & Resources

Drawings

Drawing 1000570183_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Specialty Wire and Cable
Series	100057
Description	Temp-Flex High-Performance Flat-Ribbon Cable, 3 Circuits, 1.27mm Pitch, 28 AWG, Silver Plated Copper, UL 20424, 7/36 Stranded Extruded FEP, Blue with Blue Polarity Stripe
Product Family	Temp-Flex Flat Ribbon Cable Solutions
Product Name	Temp-Flex
UPC	889056601399

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	300V AC

Physical

Cable Length	400 ft/spool, 10 ft min length, Any lengths/spool max
Circuits (Loaded)	3
Color - Cable Jacket	Blue w/Blue Polarity Stripe
Insulation	FEP
Material - Outer Jacket	FEP
Material - Plating Mating	Silver
Net Weight	9.356/g
Packaging Type	Spool
Pitch - Mating Interface	1.27mm
Temperature Range - Operating	-65° to +200°C
Wire/Cable Type	7/36 Stranded, High-Performance Flat-Ribbon, UL 20424
Wire Size (AWG)	28

Use with Part(s)

Description	Part Number

Use With

Molex PicoFlex

This document was generated on Jul 21, 2024