




**Part Number :** [757830132](#)

**Product Description :** iPass I/O Surface Mount Receptacle, Right-Angle, Internal Assembly with Shell, 36 Circuit, 0.38µm Gold (Au), Through Hole Option, Tail Length 1.96mm, Universal Key

**Series Number :** 75783

**Status :** Not Recommended For New Design

**Product Category :** High-Speed I/O Connectors



---

## Documents and Resources

### Drawings

[757830132 sd.pdf](#)

[PK-75783-002-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[EE-75586-001-001.pdf](#)

[SP-75586-001-001.zip](#)

### Specifications


[AS-75783-001-001.pdf](#)

[PS-75783-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34; 47
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-

	DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Not Recommended For New Design
Category	High-Speed I/O Connectors
Series	75783
Description	iPass I/O Surface Mount Receptacle, Right-Angle, Internal Assembly with Shell, 36 Circuit, 0.38µm Gold (Au), Through Hole Option, Tail Length 1.96mm, Universal Key
Application	Wire-to-Board
Comments	Positive or passive latching cable available
Component Type	Receptacle
Product Name	iPass,Mini Multi-Lane,PCI Express
Type	Pluggable
UPC	822350092364

### Agency

CSA	LR19980
UL	E29179

## Electrical

Current - Maximum per Contact	0.5A
Grounding to Panel	None
Voltage - Maximum	30V AC (RMS)/DC

## Physical

Circuits (Loaded)	36
Circuits (maximum)	36
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Copper-Nickel-Zinc, High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.012/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
PC Tail Length	1.96mm
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm

Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40° to +80°C
Termination Interface Style	Surface Mount and Through Hole
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size (AWG)	N/A

### Solder Process Data

Max-Duration	20
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

### Mates With / Use With

#### Use with Part(s)

Description	Part Number
iPass Cable Assemblies	<u>74573</u>
Internal iPass Mini SAS Double-Ended Plugs	<u>79576</u>

---

This document was generated on May 09, 2026