


COAXIAL CONNECTOR, SMPM, 50 Ohm, Straight PCB plug (male), smooth bore

81_SMPM-S50-0-S4/111_N

Properties

- Best performance-to-price ratio
- Excellent RF performance up to 65 GHz
- Small size, compact form factor
- Snap-on coupling mechanism with full detent and smooth bore
- Board-to-board solutions with bullets for axial and radial float



Product configuration		
Interface type	Gender	Standard
SMPM	plug	MIL-STD-348B

Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	SUCOPRO / Gold Plating
Outer conductor	Brass	SUCOPRO / Gold Plating
Insulator	PFA / PTFE	

Electrical data		
Impedance		50 Ω
Interface frequency		65 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 12 GHz	26 dB	1.11
12 GHz ... 18 GHz	20 dB	1.22
18 GHz ... 40 GHz	13 dB	1.58

Mechanical data		
Weight		0.24 g
Mating cycles		500
Board mounting type		surface mount
Height above PCB HA		3.4 mm

Engagement / Disengagement force		
	Engagement	Disengagement
Interface class	Smooth bore	Smooth bore

COAXIAL CONNECTOR, SMPM, 50 Ohm, Straight PCB plug (male), smooth bore

81_SMPM-S50-0-S4/111_N

Engagement / Disengagement force		
	Engagement	Disengagement
Interface force typical	11 N	6.7 N

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85246614	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
85228891	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
85246614	81_SMPM-S50-0-S4/111_NE	Single
85228891	81_SMPM-S50-0-S4/111_NM	Tape and Reel

Additional Information	
Remarks	The values provided are typical and may vary depending on factors such as the mating connector, PCB (layout), and assembly condition.

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P61081 / Date of publication: 04.12.2025 / uncontrolled copy