







P.C.B. LAYOUT



CIRCUIT DIAGRAM




Tolerances:			Date	Name	TSSE 67 x-J				
			05/06	dr					
			knitter-switch			30 08 70			Page
Revised	03/13	dr							1/2
Specifications	01/09	dr							
Modifications	Date	Name							

Specifications:

Contact rating: 50mA, 12V DC
Contact resistance: 100mOhm max.
Insulation resistance: 100MOhm min. at 500V DC
Dielectric strength: 250V, 50Hz for the duration of 1 minute
Operating temperature: -40°C to +85°C
Electrical life: min. 500 000 cycles
Operating force: N: 180 +/-50gf, color of actuator: brown
R: 260 +/-70gf, color of actuator: red
T: 360 +/-90gf, color of actuator: transparent
Mounting: on pc-board - SMD
Travel: N, R: 0.45mm +/-0.2mm
T: 0.60mm +/-0.2mm
Packaging unit: 900 pcs. / reel
Sealing: IP 67
Material: Contacts: phosphor bronze, silver plated
Terminals: brass, silver plated
Cover: stainless steel
Base: high-temp. thermoplastic nylon meets UL94V-0, washable
Stem: silicone rubber

Soldering conditions:



Tolerances:			Date	Name	TSSE 67 x-J
			05/06	dr	
			knitter-switch		30 08 70
Modifications	Date	Name	Page		
			2/2		