

Product datasheet

Specifications



Galaxy VM UPS Modular Battery Cabinet Narrow for 6 battery modules

GVMMODBCN

Overview

Presentation	Narrow modular battery cabinet with up to a 6 string modular battery capacity. To be used with the GVMMBTU modular battery string. Batteries are not included in the sku and must be purchased separately.
Lead time	Usually Ships within 2 Weeks

Main

Main Input Voltage	480 V 3 phases
Battery type	VRLA
Range of product	Galaxy VM
Range compatibility	Galaxy VM
Provided equipment	Installation guide

Batteries & Runtime

Battery location	Battery cabinet
Number of battery blocks per string	40
Number of battery free slots	6
Number of battery filled slots	0
Device mounting	Enclosed battery cabinet
Battery voltage	480 V

Physical

Colour	White
Height	197 cm
Width	37 cm
Depth	85.4 cm
Net weight	139 kg

Input

Network frequency	40...70 Hz
-------------------	------------

Conformance

Standards	EN/IEC 62040-3 FCC part 15 class A UL 1778
-----------	--

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...3333 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...40 °C
Storage altitude	0...14999.8 m
Storage Relative Humidity	0...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	215 cm
Package 1 Width	106 cm
Package 1 Length	75 cm
Package 1 Weight	164 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Total lifecycle Carbon footprint	1

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	F4c2965e-f80d-4830-8cd4-be926afb0f45
REACH Regulation	REACH Declaration

 Energy efficiency	
Energy Efficiency Optimized	Energy efficient product

Use Again

 Repack and remanufacture	
Removable battery	User replaceable
Take-back	Yes
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

