

Chip NTC Thermistors (Protection Device)

[Product Top Page](#)
[Search by Part No.](#)
[Search by Characteristics](#)
[Cross Reference](#)
[Catalog](#)
[Tech Notes](#)
[Technical Support Tools](#)
[FAQ](#)

NTCG163JF103HTDS



Applications



Automotive Grade

Features

125°C

125°C

UL

UL Certificate

AEC-Q200

AEC-Q200

Series

NTCG


Status



Production

Brand

TDK



Images are for reference only and show exemplary products.

PDF file of this page



Buy Now



Contact



Documents



RT Sheet

Size

Length(L)	1.60mm ±0.10mm
Width(W)	0.80mm ±0.10mm
Thickness(T)	0.80mm ±0.10mm
Terminal Width(B)	0.20mm Min.
Recommended Land Pattern (PA)	0.70mm ±0.10mm
Recommended Land Pattern (PB)	0.70mm ±0.10mm
Recommended Land Pattern (PC)	0.70mm ±0.10mm

Electrical Characteristics

Resistance [at 25°C]	10kΩ
Resistance Tolerance	±3%
B value (Typ.) [25/50°C]	3380K
B value (Typ.) [25/85°C]	3435K
B value (Typ.) [25/100°C]	3453K
B value Tolerance	±1%
Max. Electric Power [at 25°C]	100mW
Permissible Operating Current [at 25°C]	310μA
Thermal Dissipation Constant [at 25°C]	1mW/°C 1mW/K

Other

Max. Operating Temperature	125°C
Soldering Method	Reflow
UL File No.	E250289
AEC-Q200	Yes
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000pcs
Weight	0.005g

Products

» [Search by Part No.](#) » [Search by Characteristics](#) » [Distributor Inventory Check](#)

- » [Capacitors](#)
- » [Inductors \(Coils\)](#)
- » [EMC Components](#)
- » [RF / SAW Components and Modules](#)
- » [Voltage / Current / Temperature Protection Devices](#)
- » [Anechoic Chambers and Radio Wave Absorbers](#)
- » [Power Supplies](#)
- » [Magnets](#)
- » [Flash Storages](#)
- » [Wireless Charging](#)

Application Guides

Technical Support

Tech Library

Environment

Contact

News

» Sensors and Sensor Systems

» Ceramic Switching / Heating, Piezo Components and

Buzzers

» Transformers

» Ferrites and Accessories

» Noise Suppressing / Magnetic Sheet

» FA Systems

» Transparent Conductive Film

» Micro Modules (Substrates with Built-in ICs, Products Utilizing with SESUB)

» Solar Cells

» Biosensor

Home



About TDK



TDK Worldwide

[Terms of Use](#)

Copyright(c) 1996-2017 TDK Corporation. All rights reserved.
TDK logo is a trademark or registered trademark of TDK Corporation.

