

Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Catalog Cut Sheet
  - PDFDNFR18205B- ..
  - Part Drawings
  - PDFRight Angle..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'DNFR18-250B-L'

Your search criteria matched only one product, shown below

**DNFR18-250B-L**



- Right angle design for use in limited space applications
- Disconnect can be inserted and removed from the male tab without the use of tools for lower installed cost
- Longer barrel design for use with Panduit standard disconnect tool
- UL Flammability UL 94V -2/HB, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600 V per UL 310

Part Number	DNFR18250B-L
RoHS Compliancy Status	Compliant
Note	DNFR18250B-L replaces DNFR18250B-C
Part Description	Female Disconnect, right angle, nylon insulated, 22- 18 AWG, .250 x .032 tab size.
Product Type	Female
CSA Certified	Yes
UL Listed	Yes
Depth (In.)	0.62
Depth (mm)	15.7
Height (In.)	0.20
Height (mm)	5.1
Length (In.)	0.78
Length (mm)	19.8
Width (In.)	0.36
Width (mm)	9.1
CE Compliant	No
Insulation	Nylon
Max. Ins.	0.130
Max. Ins. (mm)	3.3
Panduit Color Code	Red
Plating Type	Tinned
Pricing Description	Female Disconnect, right angle, nylon insulated, 22 18 AWG, .250 x .032 tab size
Tab Size (In.)	0.250 x 0.032
Tab Size (mm)	6.3 x 0.8
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CT-1525‡, CT-2500‡
Wire Range	22 – 18 AWG
Wire Range (mm <sup>2</sup> )	0.5 – 1.0
Min. Order UOM	PC
Min. Order Qty.	50
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.