

Color: ■ red

Similar to illustration

Technical data	
Marking method	Thermal transfer
Marking	F31, ..., F40
Marking (number)	10
Marking direction	Vertical marking
Marking color	black
Marking type	Symbol
Marking differentiation	Consecutive symbols each strip
Delivery form	Marker card
Delivery form configuration	10 strips with 10 markers per card
Flammability class per UL94	V2

Physical data	
Marker/strip width	5 mm
Marker width	5 mm

Mechanical data	
Smear resistance	EN 60998-1:2004

Material data	
Color	red
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	9 g
Fire load	0.27 MJ



Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	50 (5) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332841429
Customs tariff number	49119900000

Product classification	
UNSPSC	55121731
eCl@ss 10.0	27-14-11-37
eCl@ss 9.0	27-14-11-37
ETIM 9.0	EC000761
ETIM 8.0	EC000761
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance


Compliance Search

Environmental Product Compliance794-618/000-005

↓

Installation Notes

Application



- Separating a strip from the WMB or WMB marker card.
- Stretching a WMB marker strip.
- Separating an individual marker from the WMB marker strip – for larger terminal blocks.
- Snapping a marking strip into the marker slot.

Marking

Snapping a WMB marker strip into the marker slot of the double marker carrier.

Snapping a marking strip into the marker slot.

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](https://www.wago.com)