BTA204S-800B

3Q Hi-Com Triac

Rev.02 - 19 March 2025 Product data sheet

1. General description

Planar passivated high commutation three quadrant triac in a SOT428 (DPAK) surface-mountable plastic package intended for use in circuits where high static and dynamic dV/dt and high dI/dt can occur. This "series B" triac will commutate the full rated RMS current at the maximum rated junction temperature without the aid of a snubber.

2. Features and benefits

- 3Q technology with superior commutation performance for improved noise immunity
- High blocking voltage capability
- High commutation capability with maximum false trigger immunity
- High immunity to false turn-on by dV/dt
- Less sensitive gate for very high noise immunity
- Planar passivated for voltage ruggedness and reliability
- Surface-mountable package
- Triggering in three quadrants only

3. Applications

- General purpose motor control circuits
- Home appliances
- Rectifier-fed DC inductive loads e.g. DC motors and solenoids

4. Quick reference data

Table 1. Quick reference data



Symbol	Parameter	Conditions		Min	Typ	Max	Unit
V_{DRM}	repetitive peak off-state voltage			-	-	800	V
$I_{T(RMS)}$	RMS on-state current	full sine wave; $T_{mb} \leq$ 107 °C; Fig. 1; Fig. 2; Fig. 3		-	-	4	A
I_{TSM}	non-repetitive peak on-state current	full sine wave; $T_{j(init)}$ = 25 °C; t_p = 20 ms; Fig. 4; Fig. 5		-	-	25	A
		full sine wave; $T_{j(init)}$ = 25 °C; t_p = 16.7 ms		-	-	27	A
T_j	junction temperature			-	-	125	°C
Static characteristics							
I_{GT}	gate trigger current	V_D = 12 V; I_T = 0.1 A; T2+ G+; T_j = 25 °C; Fig. 7		-	-	50	mA

Downloaded from Arrow.com.

Symbol	Parameter	Conditions		Min	Typ	Max	Unit
		V_D = 12 V; I_T = 0.1 A; T2+ G-; T_j = 25 °C; Fig. 7		-	-	50	mA
		V_D = 12 V; I_T = 0.1 A; T2- G-; T_j = 25 °C; Fig. 7		-	-	50	mA
I_H	holding current	V_D = 12 V; T_j = 25 °C; Fig. 9		-	-	30	mA
V_T	on-state voltage	I_T = 5 A; T_j = 25 °C; Fig. 10		-	1.4	1.7	V
Dynamic characteristics							
dV_D/dt	rate of rise of off-state voltage	V_{DM} = 536 V; T_j = 125 °C; (V_{DM} = 67% of V_{DRM}); exponential waveform; gate open circuit		1000	-	-	V/µs
dI_{com}/dt	rate of change of commutating current	V_D = 400 V; T_j = 125 °C; $I_{T(RMS)}$ = 4 A; dV_{com}/dt = 20 V/µs; (snubberless condition); gate open circuit		6	-	-	A/ms

5. Pinning information

Table 2. Pinning information

Pin	Symbol	Description	Simplified outline	Graphic symbol
1	T1	main terminal 1		
2	T2	main terminal 2		
3	G	gate		
mb	T2	mounting base; connected to main terminal 2		

6. Ordering information

Table 3. Ordering information

Type number	Package Name	Orderable part number	Packing method	Small packing quantity	Package version	Package issue date
BTA204S-800B	TO252	BTA204S-800B,118	Reel	2500	TO252N	07-Mar-2025
					TO252Q	05-Mar-2025

Type number	Marking codes	
	Assembly factory: N	Assembly factory: Q
BTA204S-800B	204S8B PJNxxxx xx	204S8B PJQxxxx xx

All information provided in this document is subject to legal disclaimers.

© WeEn Semiconductors Co., Ltd. 2025. All rights reserved


Downloaded from Arrow.com.

7. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
V_{DRM}	repetitive peak off-state voltage			-	800	V
$I_{T(RMS)}$	RMS on-state current	full sine wave; $T_{mb} \leq$ 107 °C; Fig. 1; Fig. 2; Fig. 3		-	4	A
I_{TSM}	non-repetitive peak on-state current	full sine wave; $T_{j(init)}$ = 25 °C; t_p = 20 ms; Fig. 4; Fig. 5		-	25	A
		full sine wave; $T_{j(init)}$ = 25 °C; t_p = 16.7 ms		-	27	A
I^2t	I^2t for fusing	t_p = 10 ms; SIN		-	3.1	A²s
dI_T/dt	rate of rise of on-state current	I_G = 100 mA		-	100	A/µs
I_{GM}	peak gate current			-	2	A
P_{GM}	peak gate power			-	5	W
$P_{G(AV)}$	average gate power	over any 20 ms period		-	0.5	W
T_{stg}	storage temperature			-40	150	°C
T_j	junction temperature			-	125	°C



f = 50 Hz; T_{mb} = 107 °C

Fig. 1. RMS on-state current as a function of surge duration; maximum values





Fig. 2. RMS on-state current as a function of mounting base temperature; maximum values

All information provided in this document is subject to legal disclaimers.

© WeEn Semiconductors Co., Ltd. 2025. All rights reserved


Downloaded from Arrow.com.



α = conduction angle

a = form factor = $I_{T(RMS)}$ / $I_{T(AV)}$

Fig. 3. Total power dissipation as a function of RMS on-state current; maximum values




t_p ≤ 20 ms; (1) dI_T/dt limit

Fig. 4. Non-repetitive peak on-state current as a function of pulse width; maximum values

All information provided in this document is subject to legal disclaimers.

© WeEn Semiconductors Co., Ltd. 2025. All rights reserved

Downloaded from Arrow.com.



f = 50 Hz

Fig. 5. Non-repetitive peak on-state current as a function of the number of sinusoidal current cycles; maximum values

All information provided in this document is subject to legal disclaimers.


© WeEn Semiconductors Co., Ltd. 2025. All rights reserved

Downloaded from Arrow.com.

8. Thermal characteristics

Table 5. Thermal characteristics

Symbol	Parameter	Conditions		Min	Typ	Max	Unit
$R_{th(j-mb)}$	thermal resistance from junction to mounting base	full cycle; Fig. 6		-	-	3	K/W
		half cycle; Fig. 6		-	-	3.7	K/W
$R_{th(j-a)}$	thermal resistance from junction to ambient free air	printed circuit board (FR4) mounted		-	75	-	K/W



(1) Unidirectional (half cycle)
(2) Bidirectional (full cycle)

Fig. 6. Transient thermal impedance from junction to mounting base as a function of pulse width

All information provided in this document is subject to legal disclaimers.

© WeEn Semiconductors Co., Ltd. 2025. All rights reserved

Downloaded from Arrow.com.

9. Characteristics


Table 6. Characteristics

Symbol	Parameter	Conditions		Min	Typ	Max	Unit
Static characteristics							
I_{GT}	gate trigger current	V_D = 12 V; I_T = 0.1 A; T2+ G+; T_j = 25 °C; Fig. 7		-	-	50	mA
		V_D = 12 V; I_T = 0.1 A; T2+ G-; T_j = 25 °C; Fig. 7		-	-	50	mA
		V_D = 12 V; I_T = 0.1 A; T2- G-; T_j = 25 °C; Fig. 7		-	-	50	mA
I_L	latching current	V_D = 12 V; I_G = 0.1 A; T2+ G+; T_j = 25 °C; Fig. 8		-	-	30	mA
		V_D = 12 V; I_G = 0.1 A; T2+ G-; T_j = 25 °C; Fig. 8		-	-	45	mA
		V_D = 12 V; I_G = 0.1 A; T2- G-; T_j = 25 °C; Fig. 8		-	-	30	mA
I_H	holding current	V_D = 12 V; T_j = 25 °C; Fig. 9		-	-	30	mA
V_T	on-state voltage	I_T = 5 A; T_j = 25 °C; Fig. 10		-	1.4	1.7	V
V_{GT}	gate trigger voltage	V_D = 12 V; I_T = 0.1 A; T_j = 25 °C; Fig. 11		-	0.7	1	V
		V_D = 400 V; I_T = 0.1 A; T_j = 125 °C; Fig. 11		0.25	0.4	-	V
I_D	off-state current	V_D = 800 V; T_j = 125 °C		-	0.1	0.5	mA
Dynamic characteristics							
dV_D/dt	rate of rise of off-state voltage	V_{DM} = 536 V; T_j = 125 °C; (V_{DM} = 67% of V_{DRM}); exponential waveform; gate open circuit		1000	-	-	V/µs
dI_{com}/dt	rate of change of commutating current	V_D = 400 V; T_j = 125 °C; $I_{T(RMS)}$ = 4 A; dV_{com}/dt = 20 V/µs; (snubberless condition); gate open circuit		6	-	-	A/ms

All information provided in this document is subject to legal disclaimers.

© WeEn Semiconductors Co., Ltd. 2025. All rights reserved

Downloaded from Arrow.com.



(1) T2- G-
(2) T2+ G-
(3) T2+ G+

Fig. 7. Normalized gate trigger current as a function of junction temperature




Fig. 8. Normalized latching current as a function of junction temperature





Fig. 9. Normalized holding current as a function of junction temperature



V_o = 1.27 V; R_s = 0.091 Ω
(1) T_j = 125 °C; typical values
(2) T_j = 125 °C; maximum values
(3) T_j = 25 °C; maximum values

Fig. 10. On-state current as a function of on-state voltage

All information provided in this document is subject to legal disclaimers.

© WeEn Semiconductors Co., Ltd. 2025. All rights reserved

Downloaded from Arrow.com.




Fig. 11. Normalized gate trigger voltage as a function of junction temperature

All information provided in this document is subject to legal disclaimers.


© WeEn Semiconductors Co., Ltd. 2025. All rights reserved

Downloaded from Arrow.com.

10. Package outline

Assembly factory: N

Plastic single-ended surface-mounted package (DPAK); 3 leads (one lead cropped)



Unit	A	A1	b	b1	b2	c	D1	D2	E	E1	e	e1	H_D	L	L1	L2	w	y
mm min	2.22	0.46	0.71	0.72	5.00	0.20	5.98	4.00	6.47	4.45	2.285	4.57	9.60	2.90 (Ref.)	0.50	0.50	0.20	
mm nom																		
mm max	2.38	0.93	0.89	1.10	5.46	0.56	6.22	---	6.73	---			10.40		---	0.90		0.20


All information provided in this document is subject to legal disclaimers.


© WeEn Semiconductors Co., Ltd. 2025. All rights reserved

Downloaded from Arrow.com.

Assembly factory: Q

Plastic single-ended surface-mounted package (DPAK); 3 leads (one lead cropped) TO252





Recommended Footprint

SYMBOLS	DIMENSION IN MM		
	MIN	NOM	MAX
A	2.184	2.286	2.400
A1	0.000	---	0.200
A2	0.889	1.041	1.170
b	0.635	0.762	0.889
b1	0.680	0.840	1.143
b2	4.953	5.340	5.500
c	0.450	0.508	0.610
c1	0.450	0.508	0.630
D	5.969	6.096	6.223
D1	5.210	5.249	5.380
E	6.350	6.604	6.800
E1	4.318	4.826	4.920
e	2.286BSC		
e1	4.572BSC		
H	9.398	10.033	10.500
L	1.270	1.520	2.032
L1	2.921REF		
L2	0.408	0.508	0.608
L3	0.889	1.016	1.270
L4	0.600	---	1.016

All information provided in this document is subject to legal disclaimers.

© WeEn Semiconductors Co., Ltd. 2025. All rights reserved

Downloaded from Arrow.com.

11. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.
[2] The term 'short data sheet' is explained in section "Definitions".
[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.ween-semi.com.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. WeEn Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local WeEn Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between WeEn Semiconductors and its customer, unless WeEn Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the WeEn Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, WeEn Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. WeEn Semiconductors takes no responsibility for the content in this document if provided by an information source outside of WeEn Semiconductors.

In no event shall WeEn Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, WeEn Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of WeEn Semiconductors.

Right to make changes — WeEn Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — WeEn Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an WeEn Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. WeEn Semiconductors and its suppliers accept no liability for inclusion and/or use of WeEn Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. WeEn Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using WeEn Semiconductors products, and WeEn Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the WeEn Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

WeEn Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using WeEn Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). WeEn does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific WeEn Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. WeEn Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without WeEn Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond WeEn Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies WeEn Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond WeEn Semiconductors' standard warranty and WeEn Semiconductors' product specifications.

All information provided in this document is subject to legal disclaimers.

© WeEn Semiconductors Co., Ltd. 2025. All rights reserved

Downloaded from Arrow.com.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

All information provided in this document is subject to legal disclaimers.

© WeEn Semiconductors Co., Ltd. 2025. All rights reserved

Downloaded from Arrow.com.

12. Contents

1. General description....1
2. Features and benefits....1
3. Applications....1
4. Quick reference data....1
5. Pinning information....2
6. Ordering information....2
7. Limiting values....3
8. Thermal characteristics....6
9. Characteristics....7
10. Package outline....10
11. Legal information....11

© WeEn Semiconductors Co., Ltd. 2025. All rights reserved

For more information, please visit: http://www.ween-semi.com
For sales office addresses, please send an email to: salesaddresses@ween-semi.com
Date of release: 19 March 2025

Downloaded from Arrow.com.