

COAXIAL CONNECTOR, BNC, 50 Ohm, Right angle cable plug (male)
16_BNC-50-3-26/133_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration		
Interface type	Gender	Standard
BNC	plug	IEC 61169-8_MIL-STD-348A/301_CEECC 22120

Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	4 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 2.5 GHz	32 dB	1.052
2.5 GHz ... 4 GHz	19 dB	1.253

Mechanical data	
Weight	0.0161 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	crimped

COAXIAL CONNECTOR, BNC, 50 Ohm, Right angle cable plug (male)

16_BNC-50-3-26/133_N

Environmental data	
Operation temperature	-65 °C ... 165°C

Ordering Information Table		
Item number	Item description	Packaging type
84057664	16_BNC-50-3-26/133_NE	Single

Suitable cables	
Cable group	U9 - 3 mm / 50 Ohm
	U41 - 3 mm / 50 Ohm
	U11 - 3 mm / 50 Ohm
Suitable cables	G_03232_D-01
	ENVIROFLEX_142
	RG_223_/U
Additional cables	RG_400_/U
	RADOX_RF_400

Additional Information	
Remarks	El. optimized for cable RG_223_/U
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3159 / Date of publication: 25.11.2023 / uncontrolled copy