

# Data Sheet | Item Number: 713-1429/117-000



THR male header, 2-row; 0.8 x 0.8 mm solder pin; angled; 100% protected against mismatching; Threaded flange; Pin spacing 3.5 mm; 18-pole; black

<https://www.wago.com/713-1429/117-000>



Color: ■ black

Similar to illustration



Dimensions in mm

$L = [(pole\ no./2) - 1] \times pin\ spacing + 13.6\ mm$

Male connector, 713 Series, solder pin dimensions 0.8 x 0.8 mm

Our male connector (item number 713-1429/117-000) simplifies electrical installations. Dimensions: (41.6 x 15.7 x 13.5) mm (width x height x depth).

Tin is used for coating the contact surfaces. The pcb connector is designed for THR soldering.

## Notes

## Safety Information

The MCS – MULTI CONNECTION SYSTEM includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors must not be connected/disconnected when live or under load. When used as intended, these connectors must not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.

## Variants:

Other pole numbers  
Other solder pin lengths  
Gold-plated or partially gold-plated contact surfaces  
Other versions (or variants) can be requested from WAGO Sales or configured at <https://configurator.wago.com/>.

## Electrical data

Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	80 V	160 V	250 V
Rated impulse withstand voltage	2.5 kV	2.5 kV	2.5 kV
Rated current	10 A	10 A	10 A

Approvals per	UL 1059		
Use group	B	C	D
Rated voltage	150 V	50 V	-
Rated current	10 A	10 A	-

Approvals per	CSA		
Use group	B	C	D
Rated voltage	150 V	-	-
Rated current	12 A	-	-

## Connection Data

Total number of potentials	18
Number of connection types	1
Number of levels	2

## Connection 1

Pole number	18
-------------	----

## Physical data

Pin spacing	3.5 mm / 0.138 inches
Width	41.6 mm / 1.638 inches
Height	15.7 mm / 0.618 inches
Height from the surface	13.3 mm / 0.524 inches
Depth	13.5 mm / 0.531 inches
Solder pin length	2.4 mm
Solder pin dimensions	0.8 x 0.8 mm
Plated through-hole diameter (THR)	1.3 (+0.1) mm

## Mechanical data

Variable coding	Yes
Anti-rotation protection	Yes

### Plug-in connection

Contact type (pluggable connector)	Male connector/plug
Connector (connection type)	for PCB
Mismating protection	Yes
Mating direction to the PCB	0°
Locking of plug-in connection	Threaded flange

### PCB contact

PCB contact	THR
Solder pin arrangement	over the entire male connector (in-line)
Number of solder pins per potential	1

### Material data

Note (material data)	<a href="#">Information on material specifications can be found here</a>
Color	black
Material group	I
Insulation material (main housing)	Polyphthalamide (PPA GF)
Flammability class per UL94	V0
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact Plating	Tin
Fire load	0.105 MJ
Weight	6 g
MSL per J-STD 020D	1

### Environmental requirements

Limit temperature range	-60 ... +100 °C
Processing temperature	-35 ... +60 °C

### Commercial data

Product Group	3 (Multi Conn. System)
PU (SPU)	25 pcs
Packaging type	Box
Country of origin	PL
GTIN	4050821156628
Customs tariff number	85366930000

### Product Classification

UNSPSC	39121409
eCl@ss 10.0	27-44-04-02
eCl@ss 9.0	27-44-04-02
ETIM 9.0	EC002637
ETIM 10.0	EC002637
ECCN	NO US CLASSIFICATION

## Environmental Product Compliance

RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	6(c)
SCIP notification number (Austria)	eff24fb6-5718-4f24-97a5-7710940a2986
SCIP notification number (Belgium)	9ec73228-913b-4a74-8408-be9e06146b9a
SCIP notification number (Bulgaria)	f353a323-21e0-4f84-b57d-61188f19f321
SCIP notification number (Czech Republic)	5da01a77-e7d9-44a5-bc25-1f30c32dd699
SCIP notification number (Denmark)	9a95b775-a98b-4876-bcd4-a71c846a9a91
SCIP notification number (Finland)	e9f4f86c-48f8-4fb3-b1b2-ad1c5709a177
SCIP notification number (France)	45169577-b06a-40d4-8a06-4970ee55c1f6
SCIP notification number (Germany)	36809b51-cfd9-4513-88db-d89c70d5bb39
SCIP notification number (Hungary)	ee7d2e02-c677-4e6f-82a3-ce923136616c
SCIP notification number (Italy)	1fb0ee51-a999-404b-8dfa-310d2c6d4532
SCIP notification number (Netherlands)	c614f0a8-33cf-4b61-a771-d886cdf548f4
SCIP notification number (Poland)	3cc4e4a6-a631-464a-b91c-eea7cfc9b9a
SCIP notification number (Romania)	b008c2a9-0779-4c3f-b9d9-191cf4281bd8
SCIP notification number (Sweden)	9f631b92-3af6-4dc4-8288-68d11e9e788b

## Approvals / Certificates

### General approvals



Approval	Standard	Certificate Name
CB DEKRA Certification B.V.	IEC 61984	NL-102427
CSA CSA Group	C22.2	2315087
KEMA/KEUR DEKRA Certification B.V.	EN 61984	71-133740

## Downloads

### Environmental Product Compliance

#### Compliance Search

Environmental Product Compliance 713-1429/117-000	↓
--	---

## Documentation

### Additional Information

Technical Section	03.04.2019	pdf 2027.26 KB	↓
		pdf 535.32 KB	↓

## CAD/CAE-Data

### CAD data

2D/3D Models  
713-1429/117-000



### CAE data

ZUKEN Portal  
713-1429/117-000



## PCB Design

Symbol and Footprint  
via SamacSys  
713-1429/117-000



Symbol and Footprint  
via Ultra Librarian  
713-1429/117-000



## 1 Compatible Products

### 1.1 System counterpart

#### 1.1.1 Female connector/socket



##### Item No.: [713-1109/107-000](#)

1-conductor female connector, 2-row; CA-GE CLAMP®; 1.5 mm<sup>2</sup>; Pin spacing 3.5 mm; 18-pole; 100% protected against mismatching; Screw flange; black

## 1.2 Optional Accessories

### 1.2.1 Coding

#### 1.2.1.1 Coding




##### Item No.: [714-101](#)

Coding key; orange

## Installation Notes

### Coding



Coding a male header by inserting a coding pin.