



Vinyl Electrical Tapes – Vinyl Tape for Corrosion Protection

HTAPE-WRAP25-100x30

HelaTape Wrap 25, Article number: 710-00803



This product is not available anymore.

Alternative product available

Please click here to get to the alternative product **HTAPE-WRAP25-100x30** - 710-10803. >
Compare this product with its replacement. >

Features

- Special adhesive with excellent protection against corrosion
- Complete environmental, mechanical and electrical protection
- Highly resistant to UV, water, oil, most chemicals, bacteria and fungus
- Used for pipes, tubes, and conduits in outside and underground applications

Certifications & Approvals



Application

This is a PVC tape with a special adhesive. This tape offers an excellent protection against corrosion and gives complete environmental, mechanical and electrical protection for all types of pipe wrapping applications. It is also resistant to UV, bacteria and fungus. HelaTape Wrap can be used for outside and underground applications.

HelaTape Wrap 25 is suitable for following markets and industries

- Electrical Installation

Electronics Industry

Telecommunication

Wind Energy Sector

Chemical Industry

Offshore Industry

Solar Energy Sector

Shipbuilding

Automotive Industry

Aerospace Industry

Defence Industry

Rail Transportation Sector

More products in this product group

[Vinyl Electrical Tapes – Vinyl Tape for Corrosion Protection](#) >

Base Data

Colour	Black (BK)
Description Short (BMEcat) (max. 150 characters)	PVC Electrical Insulation Tape 0.25 thick / 100mm x 30m black
GLOBAL PART DESCRIPTION	HTAPE-WRAP25-100x30-PVC-BK
Pack Cont.	1 Reel
Package Quantity per	reel
Product Family	HelaTape Wrap 25
Product Group	Vinyl Electrical Tapes – Vinyl Tape for Corrosion Protection



Product Dimensions



Length (L)	30 m
Thickness (T)	0.25 mm
Width (W)	100 mm

Material and Specifications



Adhesion to Backing	2.0 N/10 mm
Adhesion to Steel	2.4 N/10 mm
Breaking Strength	44 N/10 mm
Dielectric Strength	40 kV/mm
Elongation at break	200 %
ELV compliant (Article 4 - 2)	YES
Hazardous good	No
Insulating (Yes/No)	Yes
Material	Polyvinylchloride (PVC)
Operating Temperature - °C	-10 °C to +90 °C
Self extinguishing (Yes/No) ETIM	Yes
Specifications	
Suitable for high voltage (Yes/No)	No

Logistics and Packaging



More Information



ETIM 5.0	EC000128
ETIM 6.0	EC000128

Competences



Electrical Tape HelaTape

With HelaTape HellermannTyton provides a wide range of PVC- and rubber-based electrical tapes for sealing, insulation and bundling of cable and conduits.

[Electrical tape >](#)

Similar products



HTAPE-WRAP25-25x30

710-10800

Vinyl Electrical Tapes -

Downloaded from [Arrow.com](https://www.arrow.com)



HTAPE-WRAP25-50x30

710-10802

Vinyl Electrical Tapes –
Vinyl Tape for Corrosion
Protection



**HTAPE-WRAP25-
100x30**

710-10803

Vinyl Electrical Tapes –
Vinyl Tape for Corrosion
Protection

Stay in touch with us!



Global Company

About us
Worldwide
Philosophy
Environment & Quality
Corporate Social
Responsibility
Product Development
E-Business
ACADEMY
Careers
MADE FOR REAL

Products

Product overview
Cable Ties and Fixings
Insulation
Cable Protection Systems
Electrical Installation
Identification Systems
Application Tooling
Connectivity

Competences

Cable Ties
Heat Shrink Tubing
Industrial Identification
and Self-Adhesive Labels
Cable Protection
Conduits
Electrical Installation
Electrical tape
Wire connectors

- Cable rods
- Downlight covers
- Cable jointing
- Gel-filled cable joints
- Cable Tie Guns
- Connectivity Products
- RFID tracking
- Cable tie mounts
- Thermal Transfer Printer
- P-Clamp
- Wiring ducts
- Cable management high temperature applications

Markets & Industries

- Automotive Industry
- Solar plants
- Wind turbines
- Shipbuilding
- Panel building
- Rail industry
- Food Industry
- Chemical Industry
- Aerospace Industry

Media Centre

- Videos
- Product Catalogue 2018/2019
- Automotive Catalogue 2016/2017
- Connectivity Catalogues 2016/2017
- Brochures
- Software & Drivers
- Helatag & Helafix
- Templates
- Manuals & Operating Instructions

Events

Update: 03/06/2018

You can easily accept or reject the cookies on this site by choosing one of the following links:

© Heller

[I accept cookies](#)

[I refuse cookies](#)

[Contact](#) [Terms of Service](#) [Imprint](#) [Privacy Policy](#)

[Privacy statement](#)