



MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING

914CE18-Q



.071 MAX
PRETRAVEL

.980 ± .039
OPERATING
POSITION

2.480 MAX

.590

2X Ø .200 ± .010
MOUNTING HOLES
(Ø .40 C'BORE
.24 DEEP)

.300 ± .010

1.732 MAX

BRAD HARRISON
CONNECTOR M12
THREAD

Ø.280 STAINLESS
STEEL PLUNGER

NEOPRENE
SEAL


NOTES

1 - ZINC HOUSING FINISHED WITH GRAY PAINT

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	FULL	DO NOT SCALE PRINT
		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
OPERATING FORCE — — — — 5 LB MAX	CONTACT ARRANGEMENT S P D T	ONE PLACE	(.0)	±.030
DIFFERENTIAL TRAVEL — — — .004 MAX		TWO PLACE	(.00)	±.015
OVERTRAVEL — — — — .118 MIN	5A - 250 VAC 1/10HP - 125 OR 250 VAC  	THREE PLACE	(.000)	±.005
		ANGLES		±
		WEIGHT		

914CE18-Q

M

DRAWING
NUMBER

1

ISSUE

RELEASE NO. CO-69061 REPLACES

CHECK

REVISIONS

CHECK

CHECK

91

OCT

11

SAV

DRAWN

DDM/CAD