CGA3E2C0G1H221J080AD

TDK Item Description : CGA3E2C0G1H221JT***B

Lead Free | Halogen Free | REACH | RoHS COMPLIANT

Equivalent C1608C0G1H221J for Automotive


Characterization Sheet (Multilayer Ceramic Chip Capacitors)

Application & Main Feature

Automotive Grade (Counductive Epoxy Application)

Series

CGA3(1608) [EIA CC0603]



Dimensions

L	1.60mm +/-0.15mm
W	0.80mm +/-0.15mm
T	0.80mm +/-0.15mm
B	0.20mm Min.
G	0.30mm Min.

Temperature Characteristic

C0G (-55 to 125 degC 0+/-30ppm/degC)

Rated Voltage

1H (50Vdc)

Capacitance

220pF

Capacitance Tolerance

J (+/-5%)

Q Factor


1000 Min.


Insulation Resistance


10Gohm Min.


AEC-Q200

Yes









TDK

All specifications are subject to change without notice.

January 4, 2016

Downloaded from Arrow.com.