molex



Part Number : 1202530155
Product Description : Contrinex Inductive Sensor, M18 Housing, 0 - 20mm Operating Distance, Non-embeddable, Analog, 0 - 10V Output, 2m 4-wire PUR Cable, 51mm Housing Length
Series Number : 120253
Status : Not Recommended For New Design
Product Category : Inductive and Photoelectric Sensors
Engineering Part Number : DW-AD-519-M18-390

Documents and Resources

Specifications

1202530154-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025) SCIP:54196ff5-ff2e-411e-a18a-d2deb7ad4939
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M18 Housing, 0 - 20mm Operating Distance, Non-embeddable, Analog, 0 - 10V Output, 2m 4-wire PUR Cable, 51mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130063253

Electrical

Output	0-10V
Polarity	Analog

Physical

Connection	Cable (PUR 2m, 4-wire)
Length	51mm
Material - Housing	Chrome Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Non-embeddable

Downloaded from Arrow.com.

Operating Distance	0 - 20mm
Output	0-10V
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +70°C

Downloaded from Arrow.com.