

RG58 LSFH type, 50 Ohm, 1 GHz, 85°C, Ø4.95 mm, LSFH jacket

Enviroflex_B58

Properties

- Halogen free alternative to RG_58
- Low smoke
- Ozone, UV and weathering resistance



Construction			
Component	Material	Detail	Diameter
Centre conductor	Copper, Tin plated	Strand-19	0.9 mm
Dielectric	PE (Polyethylene)		2.95 mm
Outer conductor	Copper, Tin plated	Braid, 94%	3.5 mm
Jacket	LSFH (modified polyethylene)	RAL 9005 - bk	4.95 mm +/- 0.15 mm

Electrical data	
Impedance	50 Ω +/- 2Ω
Operating frequency	≤ 1 GHz
Capacitance	101 pF/m
Velocity of signal propagation	66 %
Signal delay	5 ns/m
Screening effectiveness	40 dB at frequency 1 GHz ... 3GHz
Insulation resistance	100000000 MΩ*m
Inner conductor resistance	41 Ω/km
Operating Voltage (at sea level)	≤ 2.5 kVrms
Test voltage (50 Hz/1 min)	≤ 5 kVrms

Mechanical data	
Weight	approx. 38 g/m
Static bending radius	≥ 25 mm
Repeated bending radius	40 mm
Dynamic bending radius	< 50 mm

Environmental data	
Operation temperature	-40 °C ... 85 °C
Installation temperature	-20 °C ... 60 °C
Fire characteristics	free of halogenes

RG58 LSFH type, 50 Ohm, 1 GHz, 85°C, Ø4.95 mm, LSFH jacket
Enviroflex_B58

Environmental data			
Cold bend test		MIL-C-17 § 4.8.19	
Suitable connectors			
Cable group		U7	
Ordering information			
Item number	Item description		Available as assembly only
85086965	ENVIROFLEX_B58		No
Power Matrix			
Calculation: typical Attenuation [formula: (a*f^0.5 + b*f)] and maximum Power CW [formula: (p/f^0.5)]			
a coefficient typical =	0.3455	b coefficient typical =	0.2373
fmax =	1	P at 1 GHz =	105
Frequency	Nom. attenuation	Nom. attenuation	CW power
GHz	(dB/m)	(dB/ft)	(W)
	sea level 25°C ambient temperature	sea level 25°C ambient temperature	sea level 40°C ambient temperature
0.10	0.133	0.041	332
0.20	0.202	0.062	235
0.30	0.260	0.079	192
0.40	0.313	0.096	166
0.60	0.410	0.125	136
0.80	0.499	0.152	117
1.00	0.583	0.178	105

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1109 / Date of publication: 08.08.2024 / uncontrolled copy