



1500W Modified Sine Wave DC-AC Power Inverter **A-301/302-1K7** series



■ Features :

- 12V or 24V DC input
- Power ON-OFF switch
- Input voltage range: -15% ~ +25%
- Output voltage regulation: ±10%
- Protections: Bat. Low alarm/Bat. Low shutdown/Over voltage/Over temp./Output short/Input polarity reverse/Over load.
- Output waveform: Modified sine wave
- Cooling fan ON-OFF control
- ON/OFF remote control(Optional)
- Approvals: e13/ CE
- 1 year warranty



SPECIFICATION

ORDER NO.		A301-1K7-B2	A301-1K7-F3	A302-1K7-B2	A302-1K7-F3
OUTPUT	SAFETY MODEL NO.	A-1700W			
	AC VOLTAGE	110V	230V	110V	230V
	RATED POWER	1500W			
	PEAK POWER	1700W 30min.			
	SURGE POWER	3000W			
	WAVEFORM	Modified Sine Wave			
	FREQUENCY	60Hz±1%	50Hz±1%	60Hz±1%	50Hz±1%
	AC REGULATION	±10%		±10%	
	STANDARD RECEPTACLES	TYPE-2* 3ea	TYPE-3* 2ea	TYPE-2* 3ea	TYPE-3* 2ea
LED INDICATOR	Green LED for power on; Red LED for power failure status				
INPUT	DC CURRENT	170A		85A	
	NO LOAD CURRENT DRAW	0.6A		0.36A	
	DC VOLTAGE	12V		24V	
	VOLTAGE RANGE	10 ~ 15VDC		21 ~ 30VDC	
	EFFICIENCY (Typ.)	82%		85%	
	DC CONNECTOR	1000mm R type terminal		1000mm R type terminal	
	FUSE	30A*10		20A*10	
PROTECTION	BAT. LOW ALARM	10±0.5V		21±0.8V	
	BAT. LOW SHUTDOWN	9.5±0.5V		20±0.8V	
	OVER LOAD	>1700W shut down o/p voltage, re-power on to recover			
	OVER VOLTAGE	15 ~ 16V		29 ~ 31V	
	OVER TEMPERATURE	60±5℃ / 140±9°F			
	OUTPUT SHORT	Shut-off			
	BAT. POLARITY	By fuse open			
ENVIRONMENT	WORKING TEMP.	0 ~ 30℃ @ 100% load, 40℃ @70% load			
	WORKING HUMIDITY	20% ~ 90% RH non-condensing			
	STORAGE TEMP., HUMIDITY	-30 ~ +70℃ / -22 ~ +158°F, 10 ~ 95% RH			
	TEMP. COEFFICIENT	±0.05% / °C (0 ~ 50℃)			
SAFETY & EMC	ISOLATION RESISTANCE	I/P-O/P:100M Ohms / 500VDC / 25℃ / 70% RH			
	EMI RADIATION	Compliance to EN55022 class B, 72/ 245/ CEE, 95/ 54/ CE			
	EMS IMMUNITY	Compliance to EN61000-4-2,3			
OTHERS	LVD	Compliance to EN60950			
	MTBF	86852Khrs min. MIL-HDBK-217F (25℃)			
	DIMENSION	455*210*85mm (L*W*H)			
	PACKING	5.5kg; 3pcs / 19.6kg / CARTON			
	COOLING	>40℃ (NTC) fan on			
	APPLICATIONS	Home appliance, Power tools, Office and Portable equipment and Vehicle ...etc.			

■ AC Output Receptacles (optional)


TYPE-1	TYPE-2	TYPE-3	TYPE-4	TYPE-5	TYPE-6
JAPAN	USA	EUROPE	UNIVERSAL	AUSTRALIA	U.K



1500W Modified Sine Wave DC-AC Power Inverter **A-301/302-1K7** series

Mechanical Specification

Unit:mm



File Name: A-301/302-1K7-SPEC 2016-04-06