


DSA30C100PB

100 V, 30 A Schottky Rectifier Diode

RoHS

**Features**


- Very low V_F
- Extremely low switching losses
- Low I_{RM} values
- Improved thermal behavior
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching
- Terminals finish: 100% pure tin
- Epoxy meets UL 94 V-0

Applications

- Rectifiers in Switch Mode Power Supplies (SMPS)
- Free wheeling diode in low voltage converters

Product Summary

Characteristic	Value	Unit
V_{RRM}	100	V
I_{FAV}	2 x 15	A
V_F	0.73	V

Pinout Diagram (TO-220-3L AB)

C: Cathode; **A:** Anode; **tab:** Cathode

Maximum Ratings ($T_A = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Characteristics	Condition	Max.	Units
V_{RRM}	Peak Repetitive Reverse Voltage	-	100	V
V_{RWM}	Working Peak Reverse Voltage			
V_R	DC Blocking Voltage			
I_{FAV}	Average Rectified Forward Current	50% duty cycle @ $T_c = 155^\circ\text{C}$, rectangular wave form	15 (Per Leg)	A
I_{FSM}	Peak One Cycle Non-Repetitive Surge Current (Per Leg)		30 (Per Device)	
P_{tot}	Total Power Dissipation	$T_c = 25^\circ\text{C}$	340	A
			35	W

Electrical Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Characteristics	Conditions	Typ.	Max.	Units
V_{F1}	Forward Voltage Drop (Per Leg) ¹	@ 15 A, Pulse, $T_{VJ} = 25^\circ\text{C}$	—	0.91	V
V_{F2}		@ 15 A, Pulse, $T_{VJ} = 125^\circ\text{C}$	—	0.73	V
I_{R1}	Reverse Current (Per Leg) ¹	@ $V_R = \text{rated } V_R$, $T_{VJ} = 25^\circ\text{C}$	—	250	uA
I_{R2}		@ $V_R = \text{rated } V_R$, $T_{VJ} = 125^\circ\text{C}$	—	12.5	mA
C_T	Junction Capacitance (Per Leg)	@ $V_R = 12 \text{ V}$, $T_c = 25^\circ\text{C}$ $f_{SIG} = 1 \text{ MHz}$	223	—	pF

Note 1: Pulse width < 300 μs , duty cycle < 2%

Thermal-Mechanical Specifications

Symbol	Characteristics	Condition	Specification	Units
T_{VJ}	Junction Temperature	—	-55 to +175	$^\circ\text{C}$
T_O	Operation temperature	—	-55 to +150	$^\circ\text{C}$
T_{stg}	Storage Temperature	—	-55 to +150	$^\circ\text{C}$
M_D	Mounting torque	—	Min 0.4 Max 0.6	Nm
F_c	Mounting force with clip	—	Min 20 Max 60	N
R_{thJC}	Maximum Thermal Resistance Junction to Case	DC operation	1.75	K/W
R_{thCS}	Typical Thermal Resistance Case to Heat Sink	—	0.5	K/W
wt	Approximate Weight	—	2	g

Characteristic Curves

Fig. 1. Typical Forward Characteristics




Fig. 2. Typical Reverse Characteristics






Fig. 3. Typical Junction Capacitance




Part Outline Drawing (TO-220-3L AB)



Symbol	Inches			Millimeters		
	Min.	Typical	Max.	Min.	Typical	Max.
A	0.140	—	0.190	3.56	—	4.83
A1	0.020	—	0.055	0.51	—	1.40
A2	0.080	—	0.115	2.03	—	2.92
b	0.015	—	0.040	0.38	—	1.02
b1	0.045	—	0.070	1.14	—	1.78
c	0.012	—	0.024	0.31	—	0.61
D	0.560	—	0.650	14.22	—	16.51
D1	0.330	—	0.371	8.38	—	9.42
E	0.380	—	0.420	9.65	—	10.67
e	—	0.100	—	—	2.54	—
e1	—	0.200	—	—	5.08	—
H1	0.230	—	0.270	5.84	—	6.86
L	0.500	—	0.580	12.70	—	14.73
L1	—	—	0.250	—	—	6.35
ØP	—	0.140	—	—	3.56	—
Q	0.100	—	0.135	2.54	—	3.43

Part Number and Marking




D = Diode
 S = Schottky Diode
 A = Low V_F
 30 = Forward Current (30 A)
 C = Common Cathode
 100 = Reverse Voltage (100 V)
 PB = Package Code (TO-220AB)
 YY = Year
 WW = Work Week
 S = Plant Location Code
 XXXXXXXX = Lot Number

Ordering Information

Part Number	Marking	Packing Mode	Quantity
DSA30C100PB	DSA30C100PB	Tube	50 pcs/ tube

Packing Specifications



Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.

Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.

Part of:

© 2025 Littelfuse, Inc.

 Specifications are subject to change without notice.
 Revised: TK.07/03/2025