




DETAIL B
(2-PLACES)




SECTION A-A

NOTES:

1. SPECIFICATIONS:

ELECTRICAL:
WITHSTANDING VOLTAGE: MINIMUM 1000 V RMS @ SEA LEVEL
INSULATION RESISTANCE: INITIAL 5000 MEGOHMS MAXIMUM,
1000 MEGOHMS MIN. AFTER ENVIRONMENTAL TESTING.
CONTACT RATING: 5 AMPS
CONTACT RESISTANCE: 2.7 MILLIOHMS MAX.

MATERIALS:

INSULATOR: BLACK UL94V-O RATED GLASS FILLED NYLON
CONTACT(030-1953-000): COPPER ALLOY
CONTACT AREA PLATING: GOLD OVER NICKEL,
CONNECTOR SHELL: STEEL, PLATING ZINC WITH CLEAR CHROMATE.

ENVIRONMENTAL:
OPERATING TEMPERATURE: -65°C TO +125°C


TERMINATION:
CRIMP WILL ACCOMMODATE # 20 TO 28 AWG WIRE.
TERMINATION-TOOLS:
CRIMP TOOL: M22520/2-01
INSERTION/EXTRACTION TOOL: CIET-20-HDB
POSITIONER: EP-580

2. DIMENSIONS IN [ ] ARE IN MILLIMETERS.


**DRAWING REVISIONS**

| REV | DOCUMENT | APP | DATE |
|---|---|---|---|
| A | DO 05-1094 | AKB | 1/7/06 |
| B | ECN 06E208 | | |

| NUMBER OF POSITIONS | SELECTIVE GOLD FLASH PLATING (.120" [3.05] MTG. HOLES) | | CONTACTS | DIMENSION | | | | | | | FRONT MOUNTING HOLE DIMENSIONS | | REAR MOUNTING HOLE DIMENSIONS | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| | PART NO. | FACTORY NO. | | "A" | "B" | "C" | "D" | "E" | "F" | "G" | "X" | "Y" | "X" | "Y" |
| 9 | DEUH-9S | 702 13 09 001 | INCLUDED | 1.213 [30.81] | .984 [24.99] | .640 [16.26] | .308 [7.82] | .494 [12.55] | .759 [19.28] | .422 [10.72] | .874 [22.20] | .513 [13.03] | .806 [20.47] | .449 [11.40] |
| | DEUH-9S-FO | 702 13 09 005 | NOT INCLUDED | | | | | | | | | | | |
| 15 | DAUH-15S | 702 13 15 001 | INCLUDED | 1.541 [39.14] | 1.312 [33.32] | .968 [24.59] | | | 1.083 [27.51] | | 1.202 [30.53] | | 1.134 [28.80] | |
| | DAUH-15S-FO | 702 13 15 005 | NOT INCLUDED | | | | | | | | | | | |
| 25 | DBUH-25S | 702 13 25 001 | INCLUDED | 2.088 53.04] | 1.852 [47.04] | 1.508 [38.30] | | | 1.625 [41.28] | | 1.743 [44.27] | | 1.674 [42.52] | |
| | DBUH-25S-FO | 702 13 25 005 | NOT INCLUDED | | | | | | | | | | | |
| 37 | DCUH-37S | 702 13 37 001 | INCLUDED | 2.729 [69.32] | 2.500 [64.50] | 2.156 [54.76] | | | 2.272 [57.71] | | 2.391 [60.73] | | 2.326 [59.08] | |
| | DCUH-37S-FO | 702 13 37 005 | NOT INCLUDED | | | | | | | | | | | |
| 50 | DDUH-50S | 702 13 50 001 | INCLUDED | 2.635 [66.93] | 2.406 [61.11] | 2.062 [52.37] | .420 [10.67] | .605 [15.37] | 2.178 [55.32] | .534 [13.56] | 2.297 [58.34] | .623 [15.82] | 2.218 [56.34] | .555 [14.10] |
| | DDUH-50S-FO | 702 13 50 005 | NOT INCLUDED | | | | | | | | | | | |




RECOMENDED MTG.HOLE LAYOUT
SEE CHART FOR FRONT AND REAR MTG.DIMENSIONS




CONTACT ARRANGEMENT - AS VIEWED FROM ENGAGING SIDE

**ROHS COMPLIANT**

| | | | |
|---|---|---|---|
| UNITS ENGLISH | PRO/E | Cinch | MODELED BY: V.SKUZA |
| DO NOT SCALE DRAWING | DRAWN BY V.SKUZA — DATE 06/24/05 | TITLE D*U SERIES CRIMP & POKE CONNECTOR SKT.ASS'Y(.120"MTG HOLES) | 1700 FINLEY RD LOMBARD, IL. 60148 |
| | DESIGN ENGINEER A.BALI — 06/24/05 | MATERIAL — CONTROL SPEC NUMBER | |
| | DESIGN ENGINEERING MGR. A.SHAH — 07/09/05 | MATERIAL SPEC NUMBER — FINISH — PROJECT NUMBER C14740 | |
| THIS DOCUMENT IS THE PROPERTY OF CINCH. NEITHER THIS DOCUMENT NOR ANY OF THE INFORMATION CONTAINED IN IT MAY BE DUPLICATED OR DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF CINCH. | MFG. ENGINEERING J.OCEGUERA — 07/07/05 | CAD FILE NUMBER DXUH-XXS — DRAWING NUMBER D*UH-XXS | |
| | QUALITY ASSURANCE A. VAZQUEZ — 07/06/05 | CAGE IDENT NO. 71785 — SIZE B — SCALE 1:1 — SHEET 1 OF 1 | |

Downloaded from Arrow.com.
Please read our datasheet & drawing disclaimer here.