

N-Channel JFET

PRODUCT SUMMARY			
$V_{GS(off)}$ (V)	$V_{(BR)GSS}$ Min (V)	g_{fs} Min (mS)	I_{DSS} Min (mA)
≤ -8	-25	2	2

FEATURES

- Excellent High-Frequency Gain:
Gps 11 dB @ 400 MHz
- Very Low Noise: 3 dB @ 400 MHz
- Very Low Distortion
- High ac/dc Switch Off-Isolation
- High Gain: $A_V = 60$ @ 100 μ A

BENEFITS

- Wideband High Gain
- Very High System Sensitivity
- High Quality of Amplification
- High-Speed Switching Capability
- High Low-Level Signal Amplification


APPLICATIONS

- High-Frequency Amplifier/Mixer
- Oscillator
- Sample-and-Hold
- Very Low Capacitance Switches

DESCRIPTION

The 2N3819 is a low-cost, all-purpose JFET which offers good performance at mid-to-high frequencies. It features low noise and leakage and guarantees high gain at 100 MHz.

Its TO-226AA (TO-92) package is compatible with various tape-and-reel options for automated assembly (see Packaging Information). For similar products in TO-206AF (TO-72) and TO-236 (SOT-23) packages, see the 2N4416/2N4416A/SST4416 data sheet.



Top View

ABSOLUTE MAXIMUM RATINGS

Gate-Source/Gate-Drain Voltage	-25 V
Forward Gate Current	10 mA
Storage Temperature	-55 to 150°C
Operating Junction Temperature	-55 to 150°C

Lead Temperature (l_{16} " from case for 10 sec.)	300°C
Power Dissipation ^a	350 mW

Notes

- a. Derate 2.8 mW/°C above 25°C



SPECIFICATIONS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)







Parameter	Symbol	Test Conditions	Limits			Unit	
			Min	Typ ^a	Max		
Static							
Gate-Source Breakdown Voltage	V _{(BR)GSS}	I _G = −1 μA , V _{DS} = 0 V	−25	−35		V	
Gate-Source Cutoff Voltage	V _{GS(off)}	V _{DS} = 15 V, I _D = 2 nA		−3	−8		
Saturation Drain Current ^b	I _{DSS}	V _{DS} = 15 V, V _{GS} = 0 V	2	10	20	mA	
Gate Reverse Current	I _{GSS}	V _{GS} = −15 V, V _{DS} = 0 V		−0.002	−2	nA	
		T _A = 100°C		−0.002	−2	μA	
Gate Operating Current ^c	I _G	V _{DG} = 10 V, I _D = 1 mA		−20		pA	
Drain Cutoff Current	I _{D(off)}	V _{DS} = 10 V, V _{GS} = −8 V		2			
Drain-Source On-Resistance	r _{DS(on)}	V _{GS} = 0 V, I _D = 1 mA		150		Ω	
Gate-Source Voltage	V _{GS}	V _{DS} = 15 V, I _D = 200 μA	−0.5	−2.5	−7.5	V	
Gate-Source Forward Voltage	V _{GS(F)}	I _G = 1 mA , V _{DS} = 0 V		0.7			
Dynamic							
Common-Source Forward Transconductance ^c	g _{fs}	V _{DS} = 15 V V _{GS} = 0 V	f = 1 kHz	2	5.5	6.5	mS
			f = 100 MHz	1.6	5.5		
			Common-Source Output Conductance ^c	g _{os}		f = 1 kHz	
Common-Source Input Capacitance	C _{iss}	V _{DS} = 15 V, V _{GS} = 0 V, f = 1 MHz			2.2	8	pF
Common-Source Reverse Transfer Capacitance	C _{rss}				0.7	4	
Equivalent Input Noise Voltage ^c	e _n	V _{DS} = 10 V, V _{GS} = 0 V, f = 100 Hz			6		nV/ √Hz







Notes







- a. Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.
b. Pulse test: $PW \leq 300\ \mu\text{s}$, duty cycle $\leq 2\%$.
c. This parameter not registered with JEDEC.

NH

TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

**TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)**

TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

**TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)**



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.