
THIS DRAWING IS A CONTROLLED DOCUMENT.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	T	PRODUCTION ISSUE	29JAN2019	PNT	MT






TABLE OF DIMENSIONS

PART NUMBER	H & J		K		P	R	S	T	HW & JW	KW
	Min a	Max b	Min a	Max b	±10% b	±10% b	±10% b	±10% b	±20% b	±20% b
322A112	13.2 [.52]	5.8 [.23]	6.6 [.26]	3.0 [.12]	52.3 [2.06]	26.2 [1.03]	19.3 [.76]	N/A	1.52 [.06]	1.02 [.04]
322A123	26.9 [1.06]	12.4 [.49]	6.6 [.26]	3.0 [.12]	83.3 [3.28]	41.7 [1.64]	27.2 [1.07]	10.7 [.42]	2.54 [.10]	1.02 [.04]
322A134	26.9 [1.06]	12.7 [.50]	13.2 [.52]	5.8 [.23]	107.7 [4.24]	53.8 [2.12]	38.6 [1.52]	20.3 [.80]	2.54 [.10]	1.52 [.06]
322A148	55.6 [2.19]	25.4 [1.00]	13.2 [.52]	5.8 [.23]	180.6 [7.11]	90.4 [3.56]	57.4 [2.26]	25.4 [1.00]	4.57 [.18]	1.52 [.06]
322A158	55.6 [2.19]	25.4 [1.00]	26.9 [1.06]	12.4 [.49]	222.3 [8.75]	111.3 [4.38]	77.7 [3.06]	38.1 [1.50]	4.57 [.18]	2.54 [.10]

RELEASED FOR PUBLICATION - , - .
ALL RIGHTS RESERVED.
© COPYRIGHT - TE Connectivity Ltd.
THIS DRAWING IS UNPUBLISHED.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± –
2 PLC	± –
3 PLC	± –
4 PLC	± –
ANGLES	± –

DWN PRAVEEN N T 29JAN2019
CHK N NAGAR 29JAN2019
APVD M TAYLOR 29JAN2019
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT

MATERIAL SEE SHEET 2
FINISH –

TE Connectivity Ltd.

NAME
TRANSITION, 90 DEG. SIDE BREAKOUT
—

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A4	00779	C– 322A112–XX–0THRU158–XX–0	—

CUSTOMER DRAWING

SCALE DNS SHEET 1 OF 2 REV T

1469–35 (1/15)

Downloaded from Arrow.com.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	—	—

COMPATABILITY CHART				
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
-3	Polyolefin, Semi-rigid	RT-301	/42; /86; /180	S1017; S1048; S1030
-4	Polyolefin, Flexible	RT-1304	/42; /86; /180	S1017; S1048; S1030
-12	Fluoroelastomer, Flexible	RT-1312	N/A	N/A
-25	Elastomer, Fluid Resistant	RW-2070	/42; /86; /225	S1017; S1048; S1206
-100	Polyolefin, Simi-Flexible ZEROHAL	RW-2082	/86; /180	S1048; S1030

ORDERING INFORMATION

322A1XX -XX -XX /XX -0

Base part number

Material dash number
(See Compatability Chart)

Modification number

Adhesive slash number
(If necessary, see Compatability Chart)

Color designator

NOTES

1. Dimensions appearing in table are as follows:
   a – As Supplied
   b – After Unrestricted Recovery
2. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06] max.
3. Molding ports are optional. When -00 modification number is specified molding ports will be located as shown. On size 322A112 the vent port will be eliminated.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,-,-.
© COPYRIGHT - TE Connectivity Ltd. ALL RIGHTS RESERVED.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

DWN PRAVEEN N T 29JAN2019
CHK N NAGAR 29JAN2019
APVD M TAYLOR 29JAN2019
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT

MATERIAL –
FINISH –

TE Connectivity Ltd.

NAME TRANSITION, 90 DEG. SIDE BREAKOUT
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A4	00779	C- 322A112-XX-0THRU158-XX-0	—

CUSTOMER DRAWING | SCALE DNS | SHEET 2 OF 2 | REV T

Downloaded from Arrow.com.