

Copper braid

Copper braid for EMC-compliant screening protects the cable from interferences transmitted by other electrical fields, also for the automotive industry (ISO-TS approved).



Interference signals



Temperature-resistant

Application range

EMC-compliant screening
Can be used as earthing tape
Automotive industry

Included

Are delivered in 2 pieces with 50 m each

Design

Variable diameter by tightening the braid

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001182
ETIM 5.0 Class-Description: Braided hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001182
ETIM 6.0 Class-Description: Braided hose

General:

Minor differences are possible depending on the production batch

Note:

Degree of coverage: 85 % at maximum opening

Material:

Tinned-copper

Temperature range:

-30 °C to +105 °C
Max. temperature: +120 °C (short-term)

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (22.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

Copper braid

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (22.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

Copper braid

Article number	Article designation	mm ²	Diameter in mm	Number of wires x Ø (mm)	Copper index (kg/km)	PU (m)
61721370	CU 14	1.32	1 - 4	24 x 7 x 0,1	13.2	100
61721380	CU 410	4.14	4 - 10	24 x 22 x 0,1	41.4	100
61721390	CU 1020	8.29	10 - 20	48 x 22 x 0,1	81.9	100
61721395	CU 2050	18.1	20 - 50	48 x 12 x 0,2	183	100