OMRON Industrial Automation



EE-SPX303N

Photomicro sensor, slot type, 13 mm, D-ON, NPN, connector

Downloaded from Arrow.com.

Specifications

Shape	Straight
Sensing method	Through-beam with slot
Sensing distance	13 mm
Setting method	Fixed
Connection method	System connector
Output type	NPN
Operation mode	Dark-ON
Response time	5 ms
Material housing	Polycarbonate
Thread size	Other
Product Width (unpacked)	26 mm
Product Height (unpacked)	26 mm
Product Depth (unpacked)	7.4 mm
Type of light	Infrared light
Supply voltage DC	12-24 V

Downloaded from Arrow.com.

Accessories

	**EE-1001**	Accessory Connector for Photomicrosensors, 4-pin , solder terminals
	**EE-1001-1**	Connector for Photomicrosensors, 4-pin , solder terminals, bridge between L and +
	**EE-1010 2M**	Accessory Photomicro sensor EE-SPX_03, cable connector, PVC, 2m
	**EE-1010-R 2M**	Accessory photomicro sensor EE-SPX_03, cable connector, robotic PVC, 2 m
	**EE-2002**	Accessory Photomicro sensor EE-SPX_03, NPN/PNP converter and cable connector, 0.5 m

Downloads

CAD file



EE-SPX303N/403N Broad Slot-type Photomicrosensor

Datasheet

EN PDF 663 KB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 30 October, 2026. Click here for terms of use.

OMRON

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU

Downloaded from Arrow.com.