

KMQ Series

- Downsized from current downsized snap-ins KMH series
- Endurance with ripple current : 105°C 2000 hours
- Non solvent-proof type
- Pb-free design

KMQ

↑
downsized
KMH




SPECIFICATIONS

Items	Characteristics			
Category				
Temperature Range	-25 to +105°C			
Rated Voltage Range	160 to 450V _{dc}			
Capacitance Tolerance	±20% (M) (at 20°C, 120Hz)			
Leakage Current	I≤3√CV Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V) (at 20°C after 5 minutes)			
Dissipation Factor (tanδ)	Rated voltage (V _{dc})	160 to 250V	315 to 400V	420 & 450V
	tanδ (Max.)	0.15	0.15	0.20 (at 20°C, 120Hz)
Low Temperature Characteristics (Max. Impedance Ratio)	Rated voltage (V _{dc})	160 to 250V	315 to 400V	420 & 450V
	Z(-25°C)/Z(+20°C)	4	8	8 (at 120Hz)
Endurance	The following specifications shall be satisfied when the capacitors are restored to 20°C after subjected to DC voltage with the rated ripple current is applied for 2000 hours at 105°C.			
	Capacitance change	≤±20% of the initial value		
	D.F. (tanδ)	≤200% of the initial specified value		
	Leakage current	≤The initial specified value		
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1000 hours at 105°C without voltage applied.			
	Capacitance change	≤±15% of the initial value		
	D.F. (tanδ)	≤150% of the initial specified value		
	Leakage current	≤The initial specified value		


DIMENSIONS [mm]

- Terminal Code : VS (φ22 to φ35) : Standard




No plastic disk is the standard design.

- Terminal Code : LI (φ35)



PART NUMBERING SYSTEM



Please refer to "A guide to global code (snap-in type)"

◆STANDARD RATINGS

WV (Vdc)	Cap (μF)	Case size φD×L(mm)	tanδ	Rated ripple current (Arms/ 105°C, 120Hz)	Part No.	WV (Vdc)	Cap (μF)	Case size φD×L(mm)	tanδ	Rated ripple current (Arms/ 105°C, 120Hz)	Part No.
160	470	22 × 25	0.15	1.40	EKMQ161VSN471MP25S	200	1800	35 × 40	0.15	3.08	EKMQ201VSN182MA40S
	560	22 × 30	0.15	1.50	EKMQ161VSN561MP30S		2200	35 × 45	0.15	3.48	EKMQ201VSN222MA45S
	680	22 × 30	0.15	1.70	EKMQ161VSN681MP30S	250	220	22 × 25	0.15	1.00	EKMQ251VSN221MP25S
	680	25.4 × 25	0.15	1.70	EKMQ161VSN681MQ25S		270	22 × 25	0.15	1.10	EKMQ251VSN271MP25S
	820	22 × 35	0.15	2.00	EKMQ161VSN821MP35S		330	22 × 30	0.15	1.20	EKMQ251VSN331MP30S
	820	25.4 × 30	0.15	2.00	EKMQ161VSN821MQ30S		330	25.4 × 25	0.15	1.20	EKMQ251VSN331MQ25S
	820	30 × 25	0.15	2.00	EKMQ161VSN821MR25S		390	22 × 35	0.15	1.30	EKMQ251VSN391MP35S
	1000	22 × 40	0.15	2.20	EKMQ161VSN102MP40S		390	25.4 × 25	0.15	1.30	EKMQ251VSN391MQ25S
	1000	25.4 × 35	0.15	2.20	EKMQ161VSN102MQ35S		470	22 × 40	0.15	1.40	EKMQ251VSN471MP40S
	1000	30 × 25	0.15	2.20	EKMQ161VSN102MR25S		470	25.4 × 30	0.15	1.40	EKMQ251VSN471MQ30S
	1200	25.4 × 40	0.15	2.30	EKMQ161VSN122MQ40S		470	30 × 25	0.15	1.40	EKMQ251VSN471MR25S
	1200	30 × 30	0.15	2.30	EKMQ161VSN122MR30S		560	22 × 45	0.15	1.50	EKMQ251VSN561MP45S
	1200	35 × 25	0.15	2.30	EKMQ161VSN122MA25S		560	25.4 × 35	0.15	1.50	EKMQ251VSN561MQ35S
	1500	25.4 × 45	0.15	2.50	EKMQ161VSN152MQ45S		560	30 × 25	0.15	1.50	EKMQ251VSN561MR25S
	1500	30 × 35	0.15	2.50	EKMQ161VSN152MR35S		680	22 × 50	0.15	1.70	EKMQ251VSN681MP50S
	1500	35 × 30	0.15	2.50	EKMQ161VSN152MA30S		680	25.4 × 40	0.15	1.70	EKMQ251VSN681MQ40S
	1800	25.4 × 50	0.15	2.70	EKMQ161VSN182MQ50S		680	30 × 30	0.15	1.70	EKMQ251VSN681MR30S
	1800	30 × 40	0.15	2.70	EKMQ161VSN182MR40S		680	35 × 25	0.15	1.70	EKMQ251VSN681MA25S
	1800	35 × 30	0.15	2.70	EKMQ161VSN182MA30S		820	25.4 × 45	0.15	2.00	EKMQ251VSN821MQ45S
	2200	30 × 45	0.15	2.90	EKMQ161VSN222MR45S		820	30 × 35	0.15	2.00	EKMQ251VSN821MR35S
	2200	35 × 35	0.15	2.90	EKMQ161VSN222MA35S		820	35 × 30	0.15	2.00	EKMQ251VSN821MA30S
180	2700	30 × 50	0.15	3.10	EKMQ161VSN272MR50S	315	1000	30 × 40	0.15	2.20	EKMQ251VSN102MR40S
	2700	35 × 40	0.15	3.10	EKMQ161VSN272MA40S		1000	35 × 30	0.15	2.20	EKMQ251VSN102MA30S
	3300	35 × 50	0.15	3.30	EKMQ161VSN332MA50S		1200	30 × 45	0.15	2.30	EKMQ251VSN122MR45S
	390	22 × 25	0.15	1.30	EKMQ181VSN391MP25S		1200	35 × 35	0.15	2.30	EKMQ251VSN122MA35S
	470	22 × 30	0.15	1.40	EKMQ181VSN471MP30S		1500	35 × 45	0.15	2.50	EKMQ251VSN152MA45S
	560	22 × 30	0.15	1.50	EKMQ181VSN561MP30S		1800	35 × 50	0.15	2.70	EKMQ251VSN182MA50S
	560	25.4 × 25	0.15	1.50	EKMQ181VSN561MQ25S	350	150	22 × 25	0.15	0.82	EKMQ351VSN151MP25S
	680	22 × 35	0.15	1.70	EKMQ181VSN681MP35S		180	22 × 30	0.15	0.90	EKMQ351VSN181MP30S
	680	25.4 × 30	0.15	1.70	EKMQ181VSN681MQ30S		220	22 × 30	0.15	1.00	EKMQ351VSN221MP30S
	820	22 × 40	0.15	2.00	EKMQ181VSN821MP40S		220	25.4 × 25	0.15	1.00	EKMQ351VSN221MQ25S
	820	25.4 × 30	0.15	2.00	EKMQ181VSN821MQ30S		270	22 × 35	0.15	1.10	EKMQ351VSN271MP35S
	820	30 × 25	0.15	2.00	EKMQ181VSN821MR25S		270	25.4 × 30	0.15	1.10	EKMQ351VSN271MQ30S
	1000	22 × 45	0.15	2.20	EKMQ181VSN102MP45S		330	22 × 45	0.15	1.20	EKMQ351VSN331MP45S
	1000	25.4 × 40	0.15	2.20	EKMQ181VSN102MQ40S		330	25.4 × 35	0.15	1.20	EKMQ351VSN331MQ35S
	1000	30 × 30	0.15	2.20	EKMQ181VSN102MR30S		330	30 × 25	0.15	1.20	EKMQ351VSN331MR25S
	1000	35 × 25	0.15	2.20	EKMQ181VSN102MA25S		390	22 × 45	0.15	1.30	EKMQ351VSN391MP45S
	1200	25.4 × 45	0.15	2.30	EKMQ181VSN122MQ45S		390	25.4 × 40	0.15	1.30	EKMQ351VSN391MQ40S
	1200	30 × 35	0.15	2.30	EKMQ181VSN122MR35S		390	30 × 30	0.15	1.30	EKMQ351VSN391MR30S
	1200	35 × 30	0.15	2.30	EKMQ181VSN122MA30S		390	35 × 25	0.15	1.30	EKMQ351VSN391MA25S
	1500	25.4 × 50	0.15	2.50	EKMQ181VSN152MQ50S		470	25.4 × 45	0.15	1.40	EKMQ351VSN471MQ45S
	1500	30 × 40	0.15	2.50	EKMQ181VSN152MR40S		470	30 × 35	0.15	1.40	EKMQ351VSN471MR35S
	1500	35 × 30	0.15	2.50	EKMQ181VSN152MA30S		470	35 × 25	0.15	1.40	EKMQ351VSN471MA25S
	1800	30 × 45	0.15	2.70	EKMQ181VSN182MR45S		560	25.4 × 50	0.15	1.50	EKMQ351VSN561MQ50S
	1800	35 × 35	0.15	2.70	EKMQ181VSN182MA35S		560	30 × 40	0.15	1.50	EKMQ351VSN561MR40S
	2200	30 × 50	0.15	2.90	EKMQ181VSN222MR50S		560	35 × 30	0.15	1.50	EKMQ351VSN561MA30S
200	2200	35 × 40	0.15	2.90	EKMQ181VSN222MA40S		680	30 × 45	0.15	1.70	EKMQ351VSN681MR45S
	2700	35 × 50	0.15	3.10	EKMQ181VSN272MA50S		680	35 × 35	0.15	1.70	EKMQ351VSN681MA35S
	390	22 × 25	0.15	1.31	EKMQ201VSN391MP25S	350	820	30 × 50	0.15	2.00	EKMQ351VSN821MR50S
	470	22 × 30	0.15	1.45	EKMQ201VSN471MP30S		820	35 × 40	0.15	2.00	EKMQ351VSN821MA40S
	560	22 × 30	0.15	1.67	EKMQ201VSN561MP30S		1000	35 × 45	0.15	2.30	EKMQ351VSN102MA45S
	560	25.4 × 25	0.15	1.67	EKMQ201VSN561MQ25S		120	22 × 25	0.15	0.75	EKMQ351VSN121MP25S
	680	22 × 40	0.15	1.75	EKMQ201VSN681MP40S		150	22 × 30	0.15	0.82	EKMQ351VSN151MP30S
	680	25.4 × 30	0.15	1.75	EKMQ201VSN681MQ30S		180	22 × 30	0.15	0.90	EKMQ351VSN181MP30S
	820	22 × 45	0.15	2.04	EKMQ201VSN821MP45S		180	25.4 × 25	0.15	0.90	EKMQ351VSN181MQ25S
	820	25.4 × 35	0.15	2.04	EKMQ201VSN821MQ35S		220	22 × 35	0.15	1.00	EKMQ351VSN221MP35S
	820	30 × 25	0.15	2.04	EKMQ201VSN821MR25S		220	25.4 × 30	0.15	1.00	EKMQ351VSN221MQ30S
	1000	22 × 50	0.15	2.30	EKMQ201VSN102MP50S		270	22 × 40	0.15	1.10	EKMQ351VSN271MP40S
	1000	25.4 × 45	0.15	2.30	EKMQ201VSN102MQ45S		270	25.4 × 30	0.15	1.10	EKMQ351VSN271MQ30S
	1000	30 × 30	0.15	2.30	EKMQ201VSN102MR30S		270	30 × 25	0.15	1.10	EKMQ351VSN271MR25S
	1000	35 × 25	0.15	2.30	EKMQ201VSN102MA25S		330	22 × 45	0.15	1.20	EKMQ351VSN331MP45S
	1200	25.4 × 50	0.15	2.65	EKMQ201VSN122MQ50S		330	25.4 × 40	0.15	1.20	EKMQ351VSN331MQ40S
	1200	30 × 35	0.15	2.65	EKMQ201VSN122MR35S		330	30 × 30	0.15	1.20	EKMQ351VSN331MR30S
	1200	35 × 30	0.15	2.65	EKMQ201VSN122MA30S		390	25.4 × 45	0.15	1.30	EKMQ351VSN391MQ45S
	1500	30 × 40	0.15	2.80	EKMQ201VSN152MR40S		390	30 × 35	0.15	1.30	EKMQ351VSN391MR35S
	1500	35 × 30	0.15	2.80	EKMQ201VSN152MA30S		470	25.4 × 50	0.15	1.40	EKMQ351VSN471MQ50S
	1800	30 × 45	0.15	3.08	EKMQ201VSN182MR45S		470	30 × 35	0.15	1.40	EKMQ351VSN471MR35S

◆STANDARD RATINGS

WV (Vdc)	Cap (μF)	Case size φD×L(mm)	tanδ	Rated ripple current (Arms/105°C,120Hz)	Part No.	WV (Vdc)	Cap (μF)	Case size φD×L(mm)	tanδ	Rated ripple current (Arms/105°C,120Hz)	Part No.
350	470	35×30	0.15	1.40	EKMQ351VSN471MA30S	420	220	22×45	0.20	1.05	EKMQ421VSN221MP45S
	560	30×45	0.15	1.50	EKMQ351VSN561MR45S		220	25.4×35	0.20	1.05	EKMQ421VSN221MQ35S
	560	35×35	0.15	1.50	EKMQ351VSN561MA35S		220	30×30	0.20	1.05	EKMQ421VSN221MR30S
	680	30×50	0.15	1.70	EKMQ351VSN681MR50S		220	35×25	0.20	1.05	EKMQ421VSN221MA25S
	680	35×40	0.15	1.70	EKMQ351VSN681MA40S		270	25.4×40	0.20	1.25	EKMQ421VSN271MQ40S
	820	35×45	0.15	1.90	EKMQ351VSN821MA45S		270	30×30	0.20	1.25	EKMQ421VSN271MR30S
400	100	22×25	0.15	0.70	EKMQ401VSN101MP25S		270	35×25	0.20	1.25	EKMQ421VSN271MA25S
	120	22×30	0.15	0.75	EKMQ401VSN121MP30S		330	25.4×50	0.20	1.42	EKMQ421VSN331MQ50S
	150	22×30	0.15	0.88	EKMQ401VSN151MP30S		330	30×35	0.20	1.42	EKMQ421VSN331MR35S
	150	25.4×25	0.15	0.88	EKMQ401VSN151MQ25S		330	35×30	0.20	1.42	EKMQ421VSN331MA30S
	180	22×35	0.15	0.95	EKMQ401VSN181MP35S		390	30×40	0.20	1.61	EKMQ421VSN391MR40S
	180	25.4×30	0.15	0.95	EKMQ401VSN181MQ30S		390	35×35	0.20	1.61	EKMQ421VSN391MA35S
	220	22×45	0.15	1.10	EKMQ401VSN221MP45S		470	30×45	0.20	1.86	EKMQ421VSN471MR45S
	220	25.4×35	0.15	1.10	EKMQ401VSN221MQ35S		470	35×40	0.20	1.86	EKMQ421VSN471MA40S
	220	30×25	0.15	1.10	EKMQ401VSN221MP25S		560	35×45	0.20	2.10	EKMQ421VSN561MA45S
	270	22×50	0.15	1.22	EKMQ401VSN271MP50S		680	35×50	0.20	2.20	EKMQ421VSN681MA50S
	270	25.4×40	0.15	1.22	EKMQ401VSN271MQ40S	450	68	22×25	0.20	0.50	EKMQ451VSN680MP25S
	270	30×30	0.15	1.22	EKMQ401VSN271MR30S		82	22×30	0.20	0.56	EKMQ451VSN820MP30S
	270	35×25	0.15	1.22	EKMQ401VSN271MA25S		100	22×30	0.20	0.64	EKMQ451VSN101MP30S
	330	25.4×45	0.15	1.44	EKMQ401VSN331MQ45S		100	25.4×25	0.20	0.64	EKMQ451VSN101MQ25S
	330	30×35	0.15	1.44	EKMQ401VSN331MR35S		120	22×35	0.20	0.72	EKMQ451VSN121MP35S
	330	35×30	0.15	1.44	EKMQ401VSN331MA30S		120	25.4×30	0.20	0.72	EKMQ451VSN121MQ30S
	390	25.4×50	0.15	1.55	EKMQ401VSN391MP50S		150	22×40	0.20	0.79	EKMQ451VSN151MP40S
	390	30×40	0.15	1.55	EKMQ401VSN391MR40S		150	25.4×30	0.20	0.79	EKMQ451VSN151MQ30S
	390	35×30	0.15	1.55	EKMQ401VSN391MA30S		150	30×25	0.20	0.79	EKMQ451VSN151MR25S
	470	30×45	0.15	1.68	EKMQ401VSN471MR45S		180	22×45	0.20	0.87	EKMQ451VSN181MP45S
	470	35×35	0.15	1.68	EKMQ401VSN471MA35S		180	25.4×40	0.20	0.87	EKMQ451VSN181MQ40S
	560	30×50	0.15	1.90	EKMQ401VSN561MR50S		180	30×30	0.20	0.87	EKMQ451VSN181MR30S
	560	35×40	0.15	1.90	EKMQ401VSN561MA40S		220	25.4×45	0.20	1.00	EKMQ451VSN221MQ45S
	680	35×45	0.15	2.12	EKMQ401VSN681MA45S		220	30×30	0.20	1.00	EKMQ451VSN221MR30S
420	82	22×25	0.20	0.64	EKMQ421VSN820MP25S		220	35×25	0.20	1.00	EKMQ451VSN221MA25S
	100	22×25	0.20	0.66	EKMQ421VSN101MP25S		270	25.4×50	0.20	1.19	EKMQ451VSN271MQ50S
	100	25.4×25	0.20	0.66	EKMQ421VSN101MQ25S		270	30×40	0.20	1.19	EKMQ451VSN271MR40S
	120	22×30	0.20	0.81	EKMQ421VSN121MP30S		270	35×30	0.20	1.19	EKMQ451VSN271MA30S
	120	25.4×25	0.20	0.81	EKMQ421VSN121MQ25S		330	30×45	0.20	1.38	EKMQ451VSN331MR45S
	150	22×35	0.20	0.84	EKMQ421VSN151MP35S		330	35×35	0.20	1.38	EKMQ451VSN331MA35S
	150	25.4×30	0.20	0.84	EKMQ421VSN151MQ30S		390	30×50	0.20	1.55	EKMQ451VSN391MR50S
	150	30×25	0.20	0.84	EKMQ421VSN151MR25S		390	35×40	0.20	1.55	EKMQ451VSN391MA40S
	180	22×40	0.20	0.91	EKMQ421VSN181MP40S		470	35×45	0.20	1.74	EKMQ451VSN471MA45S
	180	25.4×30	0.20	0.91	EKMQ421VSN181MQ30S		560	35×50	0.20	1.90	EKMQ451VSN561MA50S
	180	30×25	0.20	0.91	EKMQ421VSN181MR25S						

◆RATED RIPLE CURRENT MULTIPLIERS

●Frequency Multipliers

Frequency(Hz)	50	120	300	1k	10k	50k
160 to 250V _{dc}	0.81	1.00	1.17	1.32	1.45	1.50
315 to 450V _{dc}	0.77	1.00	1.16	1.30	1.41	1.43