



**Part Number :** [5052703412](#)  
**Product Description :** SlimStack Board-to-Board Receptacle, 0.35mm Pitch, SSB RP Series, 0.70 or 0.80mm Mated Height, 2.00mm Mated Width, 34 Circuits, Armor Nail  
**Series Number :** 505270  
**Status :** Active  
**Product Category :** Board-to-Board Connectors



Documents & Resources


**Drawings**  
[5052703412\\_sd.pdf](#)

**3D Models and Design Files**  
[5052703412.dxf](#)  
[5052703412.pdf](#)  
[5052703412\\_stp.zip](#)

**Specifications**  
[5052700000-A01.pdf](#)  
[5052709200SPK-200.pdf](#)  
[5052700001-PS-000.pdf](#)  
[5052700003-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements  
- Eu RoHS  
- REACH SVHC

- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Board-to-Board Connectors
Series	505270
Description	SlimStack Board-to-Board Receptacle, 0.35mm Pitch, SSB RP Series, 0.70 or 0.80mm Mated Height, 2.00mm Mated Width, 34 Circuits, Armor Nail
Series Name	0.35, SSB RP
Application	Board-to-Board
Component Type	PCB Receptacle
Product Name	SlimStack
UPC	191128462044

### Electrical

Current - Maximum per Contact	0.3A, 3.0A
Voltage - Maximum	50V AC (RMS)/DC

### Physical

Circuits (Loaded)	34
Circuits (maximum)	34
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No
Mated Height	0.70mm, 0.80mm
Mated Width	2.00mm

Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	17.060/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	0.35mm
Pitch - Termination Interface	0.35mm
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
0.35mm Pitch SlimStack Board-to-Board Plugs	<u>505070</u>
0.35mm Pitch SlimStack Board-to-Board Plugs	<u>505274</u>

---

This document was generated on Mar 13, 2025