Specifications



Eaton 187046

Eaton Moeller® series M30 Potentiometer, flat front, M30, 30.5 mm, Without scale/inscription, R 1000 kΩ, P 0.5 W, Metal bezel

General specifications

PRODUCT NAME	Eaton Moeller® series M30 potentiometer
CATALOG NUMBER	187046
MODEL CODE	M30C-FR1M-BLANK
EAN	4015081821129
PRODUCT LENGTH/DEPTH	36 mm
PRODUCT HEIGHT	63 mm
PRODUCT WIDTH	46 mm
PRODUCT WEIGHT	0.055 kg
CERTIFICATIONS	IEC/EN 60947 VDE 0660
CATALOG NOTES	Without scale/inscription
GLOBAL CATALOG	187046
PRODUCT TYPE	Potentiometer

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Potentiometer
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.

Resources

CATALOGS	eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf
DECLARATIONS OF CONFORMITY	eaton-potentiometer-declaration-of-conformity-eu251540en.pdf
DRAWINGS	eaton-operating-m30-potentiometer-dimensions.eps eaton-operating-m30-dimensions-004.eps eaton-operating-m30-dimensions-006.eps eaton-operating-m30-dimensions-005.eps eaton-operating-m30-potentiometer-3d-drawing.eps eaton-general-approval-m22-symbol.eps eaton-general-m22-symbol.eps
ECAD MODEL	DA-CE-ETN.M30C-FR1M-BLANK
INSTALLATION INSTRUCTIONS	eaton-operating-devices-m30-rmq-titan-flat-front-instruction-leaflet-il047019zu.pdf IL047030ZU
MCAD MODEL	eaton-potentiometers-mcad-drawings-flatfront.dwg DA-CS-potentiometer_flatfront
WIRING DIAGRAMS	eaton-operating-potentiometer-m30-wiring-diagram.eps

Downloaded from Arrow.com.

10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
ELECTRIC CONNECTION TYPE	Screw connection
FITTED WITH:	3 individual screw terminals
POLLUTION DEGREE	3
ACCURACY	± 10 % (linear), Resistance value
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
BEZEL COLOR	Titanium
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
NUMBER OF REVOLUTIONS - MAX	1
NUMBER OF	1

Downloaded from Arrow.com.

REVOLUTIONS - MIN	
OPENING DIAMETER	30 mm
RATED INSULATION VOLTAGE (UI)	250 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
RATED POWER	0.5 VA
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0.5 W
DESIGN	Flat front
MOUNTING POSITION	As required
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION	IP66 NEMA Other
POWER CONSUMPTION	0.5 W
LIFESPAN, MECHANICAL	25,000 Operations
SHOCK RESISTANCE	Not planned
RESISTANCE	1000000 Ohm
TERMINAL CAPACITY (SOLID)	0.5 - 1.5 mm²
TERMINAL CAPACITY (STRANDED)	0.5 - 1.5 mm²
TIGHTENING TORQUE	0.5 Nm, Screw terminals

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.