

CGA9N3X7S2A106M230KB

TDK Item Description : CGA9N3X7S2A106MT****




Equivalent C5750X7S2A106M for Automotive

Application & Main Feature

Automotive Grade (Mid Voltage (100 to 630V))

Series

CGA9(5750) [EIA CC2220]



Dimensions

L 5.70mm +/-0.4mm
W 5.00mm +/-0.4mm
T 2.30mm +/-0.2mm
B 0.20mm Min.
G

Temperature Characteristic

X7S (-55 to 125 degC +/-22%)

Rated Voltage

2A (100Vdc)

Capacitance

10uF

Capacitance Tolerance

M (+/-20%)

Dissipation Factor

5% Max.


Insulation Resistance

50Mohm Min.


AEC-Q200

Yes


DC Bias Characteristic




|Z|, ESR vs. Freq. Characteristics




Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



All specifications are subject to change without notice.

January 4, 2016