







APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-	10635	RELEASED	10/12/10	



#### Applicable FPC



#### SPECIFICATIONS:

Material:  
 Insulator: Hi-temp thermoplastic, rated UL 94V-0  
 Insulator color: Natural  
 Contacts: Copper Alloy  
 Plating:  
 Tin over Copper underplate overall  
 Electrical:  
 Operating voltage: 50 VAC max  
 Current rating: 0.4 Amps max  
 Contact resistance: 30 mohms max initial  
 Insulation resistance: 500 Mohms min  
 Dielectric withstanding voltage: 500 VAC for 1 minute  
 Temperature Rating:  
 Operating temperature: -55°C to +85°C  
 Environmental:  
 Lead free, RoHS compliant.



Positions: 3 thru 60  
 A = .020 [0.50] x No. of Spaces  
 B = A + .201 [5.10]  
 C = A + .280 [7.10]  
 D = .197 [5.00] ... 03 thru 30  
 = .213 [5.40] ... 31 thru 60  
 E = D + .047 [1.20]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES			<b>ADAM TECH</b> 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
.X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			TITLE <b>ZIF FLEX CIRCUIT CONNECTOR</b> <b>SIDE ENTRY, SMT</b>		
APPROVALS DRAWN DY 10/12/10			SIZE X PART NO. PCA-6-XX-HX-3 REV. -		
CHECKED			REF: S00030T SCALE: NTS SHEET 1 OF 1		
APPROVED					