

DC Fan

60mm sq.

San Ace 60



General Specifications

- Material.....Frame: Plastics (Flammability: UL94V-0),
Impeller: Plastics (Flammability: UL94V-1)
- Expected LifeRefer to specifications (L10:Survival rate:90% at 60°C ,
rated voltage, and continuously run in a free air state)
- Lead Wire⊕red ⊖black (Sensor) yellow (Control) brown
- Storage Temperature ...-30°C to +70°C (Non-condensing)

60×60×38mm [Mass : 130g]

9GV type



Specifications The following nos. **have PWM controls, pulse sensors, and ribs.** For ribless, append "1" to the model no.


Model No.	Rated Voltage [V]	Operating Voltage Range [V]	PWM duty cycle※ [%]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Airflow [m ³ /min] [CFM]	Max. Static Pressure [Pa] [InchH ₂ O]	SPL [dB(A)]	Operating Temperature Range [°C]	Expected Life [h]
9GV0612P1G03	12	8.0 to 13.8	100	2.8	33.6	16,000	2.37 84	751 3.02	66	-20 to +70	40,000/60°C
			0	0.12	1.5	3,100	0.44 15	26 0.10	25		
9GV0612P1H03			100	2.0	24.0	14,500	2.15 76	617 2.48	63		
			0	0.1	1.2	2,700	0.40 14	21 0.09	22		
9GV0612P1M03	12	10.8 to 13.8	100	1.5	18.0	13,000	1.93 68	496 1.99	60		
			0	0.08	1.0	2,500	0.38 13	18 0.07	19		
9GV0612P1L01 (Note)			100	0.7	8.4	10,000	1.49 52.6	293 1.17	52		
			0	0.08	1.0	2,500	0.38 13	18 0.07	19		
9GV0624P1G03	24	20.4 to 27.6	100	1.4	33.6	16,000	2.37 84	751 3.02	66		
			0	0.12	2.88	6,000	0.89 31	105 0.42	38		
9GV0624P1M03 (Note)			100	0.73	17.52	13,000	1.93 68.0	496 1.99	60		
			0	0.08	3.84	6,000	0.89 31	105 0.42	38		
9GV0648P1H03	48	38 to 57	100	0.5	24	14,500	2.15 76	617 2.48	63		
			0	0.08	3.84	6,000	0.89 31	105 0.42	38		

Note : Fan does not rotate when PWM duty cycle is 0%.

※PWM Frequency : 25kHz


Models without sensors, or with pulse sensors (no PWM control function), or lock sensors are available as options. Please refer to the index (p. 477).

Dimensions (unit: mm) (With ribs)



Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)

Inlet side, Outlet side




Options (unit: mm)

Finger Guards

Model : 109-139E Surface treatment : Nickel-chrome plating (silver)
 : 109-139H : Cation electropainting (black)


Color

Inlet side, Outlet side




Resin Finger Guards

Model : 109-1003G




Resin Filter Kits

Model : 109-1003F13 (13PPI), 109-1003F20 (20PPI)
 : 109-1003F30 (30PPI), 109-1003F40 (40PPI)




Airflow - Static Pressure Characteristics

PWM Duty Cycle




9GV0612P1G03

Operating Voltage Range













9GV0612P1G03

PWM Duty - Speed Characteristics Example




9GV0612P1G03


60mm sq.**San Ace 60****60×60×38mm** [Mass : 130g]**Airflow - Static Pressure Characteristics****PWM Duty Cycle****9GV0612P1H03****9GV0612P1M03****9GV0612P1L01****Operating Voltage Range****9GV0612P1H03****9GV0612P1M03****9GV0612P1L01****PWM Duty - Speed Characteristics Example****9GV0612P1H03****9GV0612P1M03****9GV0612P1L01**




9GV0624P1G03




9GV0624P1M03




9GV0648P1H03




9GV0624P1G03




9GV0624P1M03




9GV0648P1H03



9GV0624P1G03



9GV0624P1M03



9GV0648P1H03