



**Part Number :** [1300830266](#)

**Product Description :** Woodhead POW-R-MITE Industrial Duty Cable Reel, 12/3 SOW, 7.62m (25.0') Cord Length with 15A Connector and Ball Stop

**Series Number :** 130083

**Status :** Active

**Product Category :** Electrical Reels

**Engineering Number :** 9383-1547



---

## Documents & Resources

### Drawings

[Drawing 1300830266\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Electrical Reels
Series	130083
Description	Woodhead POW-R-MITE Industrial Duty Cable Reel, 12/3 SOW, 7.62m (25.0') Cord Length with 15A Connector and Ball Stop
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-15
Product Family	Reels - Woodhead
Product Name	POW-R-MITE
Type	Cable Reel
UPC	78678835108

### Agency

CSA	LR29921
UL	E22769

### Electrical

Current - Maximum per Contact	18.0A
GFCI	No
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	120V

### Physical

Bulb Included	N/A
Cable Length	N/A
Cable Movement	Ratchet Lock
Cord Length	7.62m (25.0')
Cord Type	12/3 SOW

Depth	0.34m (13.50")
Drum Lock	Ratchet
Duty	Industrial
Guide Arm	5° increments over 270° Arc
Height	0.37m (14.50")
Lamp Type	N/A
Material - Coating	Powder Coating
Material - Housing	Cast Aluminum
Mounting Style	Rigid
Number of Conductors	3
Number of Receptacles	1
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	1.8kg (4.0 lb)
Width	244.35mm (9.620")
Wire Size (AWG)	12

---

This document was generated on Sep 22, 2024