

BMMS00131360470MX2

Search by :

Part Number

Characteristics

Cross reference




MP

?

Closed Magnetic Circuit Type
Molding Processing & for Ultra High Current

Series Pdf

Product detail		
L(mm) ±		12.6±0.2
W(mm) ±		14.2Max.
T(mm) ±		6.0Max.
Inductance(uH)		47
Tolerance(±%)		20
Test Frequency		100kHz,0.25V
RDC(Ω)Max		0.09
RDC(Ω)Typ		0.08
Isat(A)Typ		5.5
Irms(A)Typ		3.5
Operating Temperature	- 55℃~ 125℃(Including self - temperature rise)	



Products

- Power Inductor
- EMI-Common Mode Choke
- EMI-Bead
- RF-Signal Inductor
- RF-Passives/Antennas
- LAN Transformer
- Resistor & Current Sensor

Applications

- Automotive
- Industrial
- Server/DataCenter
- Communication
- Mobile and Tablet
- Computer/Laptop
- Consumer

Design Tools

- Simulation Tool
- Product Search Engine
- E-Catalogue

About Us

- Corporate Overview
- Corporate Milestones
- Core Technology
- Certificates & Awards
- Quality and Social Responsibility

Investor

- Financial Information
- Corporate governance
- Stakeholder Contacts

[Media Center](#)

[New Products](#)

[Events](#)

[Product Notices](#)

Contact Us

[Contact Info](#)

[Contact Form](#)

[Join Chilisín](#)

[Terms of Use](#)

[Privacy policy](#)

[Sitemap](#)



Inductor



Resistor



Powder

Copyrights © 2018. Chilisín. All rights reserved.