

PRODUCT DESCRIPTION CODE :

10142961-0XX LF

—Rohs COMPATIBLE

—FOR CUSTOMER CODE:
BLANK = GENERAL USE





—PACKAGING :
BLANK = BULK

—NUMBER OF POSITIONS : 04 TO 15


—MATERIAL

NOTES:

- 1 - MATERIAL:
HIGH TEMPERATURE THERMOPLASTIC
COLOR BLACK UL94 V-0
- 2 - FOR USE WITH MINITEK μ SPACE CTW TERMINALS :
AWG 22-24, SERIES 10141272 & 10148496
AWG 26-30, SERIES 10141272 & 10148496
- 3 - TO BE MATED WITH MINITEK μ SPACE HEADERS SERIES
10142963 / 10143922
- 4 - THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO ANY
SOLDER PROCESS.
- 5 - Rohs COMPATIBLE PRODUCT SPECIFICATIONS
 - a - LABELLING :
MEETS PACKAGING SPECS AS PER GS-14-920
 - b - LEGAL STATEMENT :
SEE GS-47-0004.




10142961-0XXLF (WITH CPA)




VERSION WITHOUT CPA : OVER REQUEST
PRE-LOAD CONFIGURATION : DELIVERED STATUS

spec ref -				dr	Glass-adm, Mar	2018/11/21	projection	mm	size	A3	scale	5:1
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Cyril Jeune	2019/04/26			ecn no	-		
				chr	Hyppias, Arnau	2019/04/26			product family -		rel level Released	
				appr	Beatrice Vial	2019/04/26						
surface ISO 1302	linear	0.X	±0.3	Amphenol FCI	title RECEPTACLE ASSEMBLY MINITEK μSPACE STS 1.8 TOP LATCH	dwg no 10142961	rev A					
		0.XX	±0.10									
		0.XXX	±0.005									
	angular	0°	±2°	cat. no.	-	Product - Customer Drw		sheet 1 of 3				


PART NO.	NO. OF POSN	DIM "A"
10142961-004LF	04	9.26
10142961-005LF	05	11.06
10142961-006LF	06	12.86
10142961-007LF	07	14.66
10142961-008LF	08	16.46
10142961-009LF	09	18.26
10142961-010LF	10	20.06
10142961-011LF	11	21.86
10142961-012LF	12	23.66
10142961-013LF	13	25.46
10142961-014LF	14	27.26
10142961-015LF	15	29.06




PRE-LOAD CONFIGURATION FOR TERMINAL INSERTION



FINAL LOAD CONFIGURATION WITH INSERTED TERMINAL




FULL HEADER AND RECEPTACLE ASSEMBLY CONFIGURATION




POSITION NUMBER INDICATION FOR 8POS

spec ref -				dr	Glass-adm, Mar	2018/11/21	projection	mm	size	A3	scale	4:1		
tolerance std				eng	Cyril Jeune	2019/04/26			ecn no -					
ISO 406				chr	Hyppias, Arnau	2019/04/26			product family - rel level Released					
ISO 1101				appr	Beatrice Vial	2019/04/26								
surface ISO 1302	linear	0.X	±0.3	Amphenol FCi	title	RECEPTACLE ASSEMBLY				dwg no	10142961		rev	A
		0.XX	±0.10											
		0.XXX	±0.005											
		angular	0°	±2°		cat. no.	-	Product - Customer Drw				sheet 2 of 3		




TEST PROBE Ø0.4mm COMPLIANCE



HOLE FOR TEST PROBE

DETAIL A
SCALE 20:1



RECOMMENDED LAYOUT OF TEST PROBE Ø0.4mm

spec ref -				dr Glass-adm, Mar		2018/11/21		projection	mm	size A3		scale 8:1		
tolerance std				eng Cyril Jeune		2019/04/26				ecn no -				
ISO 406				chr Hyppias, Arnau		2019/04/26				rel level Released				
ISO 1101				appr Beatrice Vial		2019/04/26								
TOLERANCES UNLESS OTHERWISE SPECIFIED				product family -										
surface ISO 1302		linear	0.X	±0.3	Amphenol FCi	title RECEPTACLE ASSEMBLY				dwg no 10142961				rev A
			0.XX	±0.10										
			0.XXX	±0.005		MINITEK μSPACE STS 1.8 TOP LATCH								
		angular	0°	±2°						cat. no. -		Product - Customer Drw		