



CODE B
PN: 35648646








CODE A
PN: 33335722














NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

   DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. FOR APPLICATION DATA SEE THE APPLICATION DRAWING.

3. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:

   TERMINAL: TERM F OCS 0.64 IDR SN 13767044 / APEX 2.8 SN 1541889I (2.5)

   MATING PART REFER TO DRAWING : 33335722_CDE01_S01_01

ASSEMBLY PART NUMBER	ASSEMBLY PART NAME	REV.	CODING	ITEM NO	PART NUMBER	PART NAME
35648646	ASM 24W FEMALE	01	B	2	33335724	TPA
				1	35648647	HOUSING
33335722	ASM 24W FEMALE	01	A	2	33335724	TPA
				1	33335723	HOUSING

SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ( ) DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	6
	LAST NO. USED	6

MISSING SYMBOLS
NO MISSING SYMBOL NUMBER

DWG STATUS DATE	STG	REV	N/P	CHG	ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
22SE22	R	01	-	-		CREATED PART DRAWING	448473	KAV	LZ	ZJ
21NO22	R	01	AA	-	-	UPDATE CODE LAYOUT	448473	LZX	LZX	

(6) PROCESS SENSITIVE DIMENSION

DIMENSIONS ENCLOSED IN ( ) INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

DIMENSIONAL RANGE (MM)										CHART M
FROM	> 0	> 6	> 30	> 70	>120	>160	>200	>250	>315	
TO	6	30	70	120	160	200	250	315	400	
TOLERANCE UNLESS OTHERWISE SPECIFIED										
	±0.1	±0.2	±0.3	±0.4	±0.45	±0.55	±0.7	±0.85	±1.05	
ANGULAR TOLERANCE ±1°										

THIRD ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

NX

A ——— LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.

PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.

CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.

DWG TYPE: PART DRAWING

STYLE

VOLUME (CM³)

DISTR CODE

UNLESS OTHERWISE SPECIFIED

THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM 2021. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.

ALL DIMENSIONS ARE IN MILLIMETERS

REFERENCE

•APTIV•

CONNECTION SYSTEMS
Chennai, India

COPYRIGHT 2022 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

	DATE
DR	
APVD1 M.KAVISUTHAN	22SE22
APVD2 LI.ZHENXIANG	22SE22
APVD3 ZHENG.JONNY	22SE22
APVD4	
APVD5	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001

MATERIAL: POLYAMIDE BLEND

DRAWING NAME: TAXI CONN 24 M APEX 2.8 OCS 0.64

DRAWING NUMBER: 35711659

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A0	5:1	1 OF 1	1 OF 1	R	01	AA

Downloaded from Arrow.com.

User: B_Bunn3
Form: 3.1_A3_TD02_0501_S01_01.dft
Path: C:\APTIV\DRAWINGS\35711659.dft
Time: 11:09:11 Date: 21-Nov-22