



Part Number : [643193219](#)

Product Description : .635mm, 1.50mm, CMC Receptacle, 32 Circuits, Right Wire Output, Brown Coding, Mat Sealed

Series Number : 64319

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[643193219 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[AS-64319-002-001.pdf](#)

[AS-64319-002-CH-001.pdf](#)

[AS-64319-002-FR-001.pdf](#)

[AS-64319-002-SP-001.pdf](#)

[984200002-AS-KR-000.pdf](#)

[AS-98420-002-001.pdf](#)

[AS-98420-002-CH-001.pdf](#)

[AS-98420-002-FR-001.pdf](#)

[AS-98420-002-SP-001.pdf](#)

[PK-64319-001-001.pdf](#)


[PS-64319-001-001.pdf](#)

[PS-64319-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
------------	-----------

China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclhexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	64319
Description	.635mm, 1.50mm, CMC Receptacle, 32 Circuits, Right Wire Output, Brown Coding, Mat Sealed
Application	Automotive, Power, Wire-to- Board
Comments	Current tested on a 5 terminals loaded connector, current for

	temperature increase of 40°C; Current max = 6.0A for 0.635mm Terminal (0.75mm ² wire) and 12.0A for 1.50mm Terminal (2.00mm ² wire)
More Detailed Tech Information	Sealed, high-density, modular connecting system for Power Train and Body Electronics applications in cars, trucks, busses
Product Name	CMC
UPC	883906134860

Physical

Circuits Detail	8 x 1.5mm & 40 x 0.635mm terminals
Circuits (maximum)	32
Color - Resin	Brown
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	29.426/g
Number of Rows	4
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm, 3.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.50mm, 3.70mm CMC Header, Right-Angle, 32 Circuits, 1 Port, Brown	<u>643340300</u>

Use with Part(s)

Description	Part Number
CMC Wire Cap for 32 Circuits, CMC Receptacle Mat Sealed	<u>643191201</u>
CMC 0.635mm Blind Cavity Plug	<u>643251010</u>
CMC 1.50mm Blind Cavity Plug	<u>643251023</u>
0.635mm CMC CP Female Terminals	<u>64322</u>
1.50mm CMC CP Female Terminals	<u>64323</u>

Application Tooling

Global

Description	Part Number
Unlocking Tool for CMC and CMX Receptacle Connector	<u>638241200</u>

This document was generated on Apr 15, 2026