




3SBC1778A2 Product Details

SharePrintEmail



Military/Aerospace High Performance Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- ? 3SBC 1/5 - Size Relay Series
- ? Input Voltage = 18 VDC
- ? Contact Arrangement = 2 Form C, DPDT, 2 C/O
- ? Contact - Rated Current = 2 A
- ? Non Polarized, Monostable Coil - Magnetic System

[View all Features](#)

Quick Links

- ? [Check Pricing & Availability](#)
- ? [Search for Tooling](#)
- ? [Product Feature Selector](#)
- ? [Contact Us About This Product](#)

3SBC1778A2
(1617073 -4)

TE Internal Number: 1617073

- 4

[Active](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information	
Product Drawings: ? None Available Catalog Pages/Data Sheets: ? None Available Product Specifications: ? None Available Application Specifications: ? None Available Instruction Sheets: ? None Available CAD Files: ? None Available	Additional Information: ? Product Line Information Related Products: ? Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? Series = 3SBC 1/5 - Size Relay ? Termination Type = Solder Hook Terminals Electrical Characteristics: ? Input Voltage (VDC) = 18 ? Contact - Rated Current (A) = 2 ? Coil Polarity Protection Diode = Without ? Transistor Driver = Without ? Coil Resistance (?) = 650 ? MOSFET Driver = Without ? Coil Power Measurement = Milliwatts ? Coil - Rated Power (mW) = 498 ? Actuating System = DC ? Shock = 75 G's, 6ms ? Vibration = 30G's, 10 to 3000Hz Contact Features: ? Mounting Options = Chassis Mount ? Enclosure Type = Hermetically Sealed	Configuration Features: ? Contact Arrangement = 2 Form C, DPDT, 2 C/O ? Coil - Magnetic System = Non Polarized, Monostable ? Coil Suppression Diode = Without Industry Standards: ? Government/Industry Qualification = Yes ? Government/Industry Part Number = M39016/13 -112L ? RoHS/ELV Compliance = Not ELV/RoHS compliant ? Lead Free Solder Processes = Not suitable for lead free processing ? Approved Standards = M39016 Qualified, L Level Conditions for Usage: ? Temperature Range (°C) = -65 - +125 Other: ? Brand = CII

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

