


## 170015 -1 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**170015 -1**

TE Part Number: 170015 -1

[Active](#)

[Add to Part List](#)

### Multiple Circuit Housings with Tabs & Receptacles Including FASTIN -FASTON

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Receptacle
- ? Tab Fit = 2.79 x 0.51 mm
- ? Wire Range = 0.50 -1.40<sup>2</sup> [20-16] mm [AWG]
- ? Insulation Diameter = 2.00 -3.00 [.079 -.118] mm [in]
- ? Receptacle Style = Straight

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [110" SERIES FASTIN FASTON RECEPTACLE](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? ['110' Series FASTIN -FASTON\\* Connector](#) (PDF, Japanese)

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files: ( [CAD Format & Compression Information](#) )

- ? [2D Drawing](#) (DXF, Version N)
- ? [3D Model](#) (IGES, Version N)
- ? [3D Model](#) (STEP, Version N)

[List all Documents](#)

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Receptacle
- ? [Tab Fit \(mm \[in\]\)](#) = 2.79 x 0.51 [.110 x .020]
- ? [Insulation Diameter \(mm \[in\]\)](#) = 2.00 -3.00 [.079 -.118]
- ? [Receptacle Style](#) = Straight
- ? [Wire/Cable Type](#) = Regular Wire
- ? [Finish](#) = None
- ? [Material](#) = Brass
- ? [Insertion Force](#) = Normal
- ? [Insulation Support](#) = With
- ? [Crimp Type](#) = F -Crimp
- ? FASTON = Yes
- ? For Housing Type = Multiple

#### Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 0.50 -1.40<sup>2</sup> [20-16]
- ? Stock Thickness (mm [in]) = 0.51 [0.020]

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- ? [Packaging Method](#) = Strip

#### Other:

- ? Line = FASTIN -FASTON .110
- ? Brand = AMP