


Part Number : 22122154
Product Description : KK 254 Solid Header, Right-Angle, with Friction Lock, 15 Circuits, 0.51µm Gold (Au) Plating, Bag
Series Number : 7478
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Part Number : A-7478-15A241

Documents and Resources

Drawings

022122154_sd.pdf

PK-7478-001-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

SYM-22-05-3151-001.zip

Specifications

PS-10-07-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	7478
Description	KK 254 Solid Header, Right-Angle, with Friction Lock, 15 Circuits, 0.51µm Gold (Au) Plating, Bag
Application	Wire-to-Board
Component Type	PCB Header
Product Name	KK 254
UPC	800753592261

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V AC

Physical

Breakaway	No
Circuits (Loaded)	15

Downloaded from Arrow.com.

Circuits (maximum)	15
Color - Resin	Natural (White)
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-0
Gender	Male
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Mounting Style	Through Hole
Net Weight	1.975/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Bag
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.58mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.508µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Partially Shrouded
Stackable	Yes
Temperature Range - Operating	-40° to +80°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE

Downloaded from Arrow.com.

Max-Cycle	1
Max-Temp	235

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 254 Single Row Crimp Housings	2695
KK 254 PC Board Connector	4455
KK 254 Receptacle Housings	7880

Downloaded from Arrow.com.