



Pushing Performance
Since 1945

Han F+B 17D SMC MI CRT



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 517 3001
Specification	Han F+B 17D SMC MI CRT
HARTING eCatalogue	https://harting.com/09155173001

Identification

Category	Inserts
Series	Han® F+B

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	17
PE contact	Yes
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm²
Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥3,000
Note on the mating cycles	Mating cycles with other HMC components

Material properties

Material (insert)	Polycarbonate (PC)
-------------------	--------------------



Pushing Performance
Since 1945

Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0

Commercial data

Packaging size	1
Net weight	15 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140186743
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522