
55A1843-22-MSL4-9CS2275 Product Details



55A1843-22-MSL4-9CS2275

TE Internal Number: 427495-000

Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Cable Type = Spec 55
- Wire Source = United States
- Cable Style = Jacketed, Round-Braid Shielded
- Wire Size (AWG/CM) = 22 AWG
- Voltage Rating = 600 VAC

View all Features

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- FOUR CONDUCTOR CABLE, RADIATION-CROSSLINKED, MODIFIE... (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Cable Style = Jacketed, Round-Braid Shielded
- Number of Conductors = Twisted Quad

Electrical Characteristics:
- Voltage Rating (VAC) = 600

Body Related Features:
- Wire Size (AWG/CM) = 22 AWG
- Cable Jacket Color = White
- Conductor Type = Nickel-Plated Copper
- Wire Color = Blue, Green, Orange, White
- Outside Diameter (mm [in]) = 3.96 [0.156]
- Wire Diameter (mm [in]) = 1.27 [0.050]
- Conductor O.D. (mm [in]) = 0.76 [0.030]

Configuration Related Features:
- Cable Type = Spec 55

Industry Standards:
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:
- Temperature Range (°C) = -65 – +200

Operation/Application:
- Application = Airframe - Medium Weight

Packaging Related Features:
- Wire Source = United States
- Wire Size - Details = 22 AWG 0.38 mm², 0.00059 in², 19 x 34 AWG
- Shield (Screen) Diameter (mm [in]) = 3.56 [0.140]

Other:
- Brand = Raychem

© 2009 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.