







AT ALL TIMES WATER RESISTANT CONNECTORS NOT IN USE SHOULD BE COVERED WITH A CONEC WATER RESISTANT CAP OR WATER TIGHT HOOD.



NOTES:

1. METALSHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 30µin HARD GOLD over min. 50µin NICKEL
4. THREADED SPACER CLIP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: $\phi 3.1 \pm 0.1$; PCB THICKNESS 1.6mm
5. COLLAR: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. FRAME: ZINC DIE CAST; NICKEL PLATED
7. HEXLOCKING SCREW: STAINLESS STEEL
8. P.C.B. HOLE DRILLINGS ON SHEET 2
9. RECOMMENDED TORQUE FOR MOUNTING SCREW 35Ncm (3.1 in.LB) / max.40Ncm (3.5 in.LB)
10. CONNECTOR IS PART MARKED: 6STD37SCR99E10X CONEC ABC

Directive 2002/95/EC
RoHS
Compliant


APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance			dim. in mm
				date	name		
				drawn	02.07.08	Lehmenkühler	
				appd.	02.07.08	Fischer	
				norm			
				d-old			
a	Origin						
rev.	description	date	name				

scale: 3:1	
material: SEE NOTES	
title: D-SUB FEMALE 37pos. SOLDER PIN STRAIGHT threaded spacer clip and hexlocking screw	
dwg no: Inventor 10	DIN-A3
15K1A249	
sh: 1	
part no: 6STD37SCR99E10X	



APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance		
dim. in mm	date	name
drawn	02.07.08	Lehmenkühler
appd.	02.07.08	Fischer
norm		
d-old		

CONEC®

scale:	3:1	
material:	SEE SHEET 1	
title:	P.C.B. HOLE DRILLINGS	
	D-SUB FEMALE 37pos. SOLDER PIN STRAIGHT	
	threaded spacer clip and hexlocking screw	
dwg no:	Inventor 10	DIN-A3
	15K1A249	sh: 2
part no:	SEE SHEET 1	