





MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING

914CE16-Q



2X ϕ .200 $\pm$.010
MOUNTING HOLES
(ϕ .40 C'BORE
.24 DEEP)


NOTES

- 1 - ZINC HOUSING FINISHED WITH GRAY PAINT
- 2 - SWITCH WILL ACTUATE IN BOTH DIRECTIONS

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 3 IN. LB MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
RELEASE FORCE — — — 6 IN. OZ MIN	5A — 250 VAC 1/10HP — 125 OR 250 VAC  	ONE PLACE	(.0)	± .030
PRETRAVEL — — — — — 30° MAX		TWO PLACE	(.00)	± .015
DIFFERENTIAL TRAVEL — — — 3° MAX		THREE PLACE	(.000)	± .005
OVERTRAVEL — — — — — 40° MIN		ANGLES		±
		WEIGHT		

914CE16-Q

M

DRAWING
NUMBER

1

ISSUE

REPLACES

RELEASE NO. CO-69061

CHECK

REVISIONS

CHECK

DDM/CAD

DRAWN

CHECK

91

OCT

29

SA

V

1982