

MATERIALS AND FINISHES

INNER BODY BRASS
PLATED TRI-MTAL (.000020) MIN OVER NICKEL (.000050) MIN

OUTER BODY BRASS
PLATED NICKEL (.000100) MIN

CENTER CONTACT BRASS
PLATED GOLD (.000010) MIN OVER NICKEL (.000100) MIN



OUTER CONTACT, COUPLING NUT, WASHER BRASS
PLATED NICKEL (.000070) MIN OVER COPPER (.000030) MIN

INSULATOR TEFLON

GASKET SILICON RUBBER

SPRING WASHER BERYLLIUM COPPER
PLATED NICKEL (.0000700) MIN OVER COPPER (.000030) MIN

RESISTOR 1 WATT, 50 OHM



PART # 73171-0910

PS-89675-0960	PRODUCT SPECIFICATION
MIL-STD-348A, FIG. 301.1	INTERFACE
SPECIFICATION	DESCRIPTION

UNLESS OTHERWISE SPECIFIED DIMS
ARE MILLIMETERS AND ANGLES ARE DEGREES.

- ALL OVER.
- NO CHATTER OR NON-UNIFORM
SURFACE FINISH ALLOWED.
- PARTS TO BE FREE OF BURRS
& SHARP EDGES 0.13(.005) MAX BREAK.
- EXTERNAL THREADS TO BE ROLLED
OR SINGLE POINT.
- DIAMETERS TO BE CONCENTRIC
WITHIN 0.08(.003) TIR.

BODY CHANGE PLATED
TRI-M WAS NICKEL

EC NO: URF2009-0479
2009/02/25
DRWN:LIN
2009/02/26
CHKD:
2009/02/27
APPR:MHUANG

QUALITY
SYMBOLS

▽=0

▽=0

REV

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .---	± .---
3 PLACES	± .---	± .---
2 PLACES	± .---	± .---
1 PLACE	± .---	± .---

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY DATE
TEF 2001/03/26

CHECKED BY DATE
SSS 2001/03/26

APPROVED BY DATE
GMH 2001/03/26

MATERIAL NO.
731710910

SIZE
C

SCALE
DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

TITLE
BNC PLUG, TERMINATION
50 OHMS
BNC-PT

MOLEX MOLEX INCORPORATED

DOCUMENT NO.
SD-73171-091

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION